

THM WO 25.4/95.2 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 8.1 - 22.3 mm, 25.4 x 95.2 mm, white
Order No.	1109140000
Type	THM WO 25.4/95.2 WS
GTIN (EAN)	4032248885299
Qty.	1 ROL

THM WO 25.4/95.2 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	25.4 mm	Height (inches)	1 inch
Width	95.2 mm	Width (inches)	3.748 inch
Net weight	421 g		

Temperatures

Operating temperature range -40...150 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Polyacrylate adhesive		
Material colour according to resistance code	9		
Type of printing	neutral		
Version	Self-adhesive		
Width	95.2 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	No		
Basic material	Polyester film		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Size of labelling field	25.4 x 25.4 mm		
Approval acc. to UL 969 compatible printer	Yes THM MULTIMARK , THM MULTIMARK PLUS		
Number of markers per combination	1 Label reel = Conductor and cable markers		
Operating temperature range	-40...150 °C		
Number per roll	1000		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	400 mm ²
Conductor cross-section, min.	0.75 mm ²	Conductor O.D., max.	22.3 mm
Conductor O.D., min.	8.1 mm	Text field width	25.4 mm
Text field height	25.4 mm	Conductor O.D.	8.1 - 22.3 mm
Cross-section for connected wire	0.75 - 400 mm ²		

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings

