

HDC HP 250 SHOCKPROTEC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The RockStar® HighPower housings are manufactured from high-strength die-cast aluminium and offer perfect protection against harsh environmental conditions thanks to continual optimisation. The multi-part housing gives users the opportunity to examine work processes down to the last step in the workflow.

General ordering data

Version	Accessories, Screw connection, Installation size: 250
Order No.	1120130000
Type	HDC HP 250 SHOCKPROTEC
GTIN (EAN)	4032248901487
Qty.	1 items

HDC HP 250 SHOCKPROTEC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Length	37 mm	Length (inches)	1.4567 inch
Diameter	12.3 mm	Net weight	2 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of connection	Screw connection	Installation size	250
UL 94 flammability rating	V-0	Colour	black
Insulation resistance	1010 Ω	Insulating material	Polyamide with fibre optic
Pollution severity	PD 2 (PD 3)	Basic material	PA 66 GF 30, Stainless steel, rust-proof
Series	HighPower	Free from halogens	false
BG	250		

General data

Type of connection	Screw connection	Colour	black
Basic material	PA 66 GF 30, Stainless steel, rust-proof	Series	HighPower

Important note

Product information: Depending on the intended operation, internally generated voltages can superimpose the working voltage and contain corresponding peaks. It is imperative to ensure that these peak voltages do not exceed the rated voltage. For applications outside of this specification, please contact us.

Classifications

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

HDC HP 250 SHOCKPROTEC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

