

**HDC HP 550 F 240****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Version	HDC insert, Female, Crimp connection, Installation size: 550
Order No.	<a href="#">112060000</a>
Type	HDC HP 550 F 240
GTIN (EAN)	4032248901609
Qty.	1 items

## HDC HP 550 F 240

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Length	98.3 mm	Length (inches)	3.8701 inch
Diameter	43 mm	Net weight	212.96 g

## Temperatures

Limit temperature	-50 °C ... 120 °C
-------------------	-------------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

## General data

Plugging cycles, silver	≥ 500	Type of connection	Crimp connection
Installation size	550	UL 94 flammability rating	V-0
Volume resistance	≤0.1 mΩ	Colour	black
Insulation resistance	1010 Ω	Insulating material	PA GF
Conductor cross-section	240 mm <sup>2</sup>	Surface finish	Silver passivated
Plugging cycles	≥ 500	Type	Female
Pollution severity	PD 2 (PD 3)	Basic material	Copper alloy
Series	HighPower	Rated impulse voltage (DIN EN 61984)	15 kV
Operating voltage, max. (total temperature=60°C)	3000 V	Free from halogens	false
Rated current acc. to DIN EN 61984 (ambient temperature=20°C)	550 A	BG	550

## Power contact

Type of connection, power contact	Crimp connection	Stripping length, performance contact	30 mm
Rated impulse voltage (DIN EN 61984), power contact	15 kV		

## Version

Stripping length, rated connection	30 mm	Type of connection	Crimp connection
Installation size	550	Volume resistance	≤0.1 mΩ
Conductor cross-section, max.	240 mm <sup>2</sup>	Conductor cross-section, min.	240 mm <sup>2</sup>
Surface finish	Silver passivated	Basic material	Copper alloy
BG	550		

## Important note

Product information	Depending on the intended operation, internally generated voltages can superimpose the working voltage and contain corresponding peaks. It is imperative to ensure that these peak voltages do not exceed the rated voltage. For applications outside of this specification, please contact us.
---------------------	---

## Technical data

### Classifications

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		

**HDC HP 550 F 240**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)



## HDC HP 550 F 240

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Accessories

[www.weidmueller.com](http://www.weidmueller.com)

### HighPower spare parts



### General ordering data

Type	HDC HP CLAMP 550A	Version	
Order No.	<a href="#">2447780000</a>	HDC-HighPower	
GTIN (EAN)	4050118461671		
Qty.	25 ST		