


## WAD 5 MC NE GE

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The WAD connector marker is suitable for W-series terminals and for the WEW 35/2 and ZEW 35/2 end brackets. The markers are available as blank markers, with custom printing or standard print with lightning symbol. The WAD MultiCard markers are suitable for labelling with PrintJet CONNECT printers. For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Version	Group markers, Cover, 33.3 x 5 mm, Pitch in mm (P): 5.00 WDU 2.5, WEW 35/2, ZEW 35/2, yellow
Order No.	<a href="#">1112920000</a>
Type	WAD 5 MC NE GE
GTIN (EAN)	4032248891771
Qty.	48 items

**WAD 5 MC NE GE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	11.74 mm	Depth (inches)	0.4622 inch
Height	33.3 mm	Height (inches)	1.311 inch
Width	5 mm	Width (inches)	0.1968 inch
Net weight	1.44 g		

**Temperatures**

Operating temperature range -40...100 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.018 kg CO2 eq.	

**General data**

Material colour according to resistance code	4		
Type of printing	neutral		
Width	5 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	yellow		
Halogen	No		
Basic material	Polyamide 66		
Number of markers per packaging unit compatible printer	Form of supply	MultiCard	
	<a href="#">PRINTJET CONNECT</a>		
Number of markers per combination	1 MultiCard = Cover		
Operating temperature range	-40...100 °C		
Application/manufacturer	WDU 2.5, WEW 35/2, ZEW 35/2		

**Connector markers**

Pitch in mm (P) 5.00 mm

**Classifications**

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

**Drawings**



**Drawing**

