

IE-C5DS4VG0015MCSA25-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

| | |
|------------|---|
| Version | System cable, M12 D-code – IP 67 straight pin, RJ45 IP 67 RockStar V05 metal, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 1.5 m |
| Order No. | 1121160000 |
| Type | IE-C5DS4VG0015MCSA25-X |
| GTIN (EAN) | 4032248902279 |
| Qty. | 1 items |

IE-C5DS4VG0015MCSA25-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|----------|-----------------|--------------|
| Length | 1.5 m | Length (inches) | 59.0551 inch |
| Net weight | 176.88 g | | |

Temperatures

| | | | |
|--------------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...80 °C | Operating temperature | -40 °C...70 °C |
| Installation temperature | -40 °C...80 °C | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6bl, 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 67cf1078-beca-4687-860b-dc475a6ec24a |

Cable specific standards

| | | | |
|--------------------------------|--|------------------------------|--------------------------|
| Standard, insulating material | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3) | Standard, wire material | DIN EN 13602 Cu-ETP-A |
| Standard, assembly | UL-Style 21694 | Standard, shielding material | DIN EN 13602 Cu-ETP-A..B |
| Standard, additional standards | UL-File E11901 Vol.1 Sec.12 Page 1, UL-File E116441 Vol.1 Sec.6 Page 8 | | |

General standards

| | |
|--------------------|---|
| Connector standard | IEC 61076-3-106 Var. 5, IEC 61076-2-101, IEC 60603-7-51 |
|--------------------|---|

Cable structure

| | | | |
|---------------------------------------|--|------------------------------|---|
| Strands | 7 | Sheathing colour | green (RAL 6018) |
| Standard designations | 2YY(ST)CY 2x2x0,75/1,5-100 LI VZN GN | Cross-section | 4*AWG 22/7 - 0.32 mm ² |
| Shielding | SF/UTP | Number of wires | 4 |
| Insulation cross-section | 1.5 mm | Insulation | PE |
| Sheath diameter, max. | 6.7 mm | Sheath diameter, min. | 6.3 mm |
| Material sheath | PVC | Filler | As central element |
| Arrangement of wire cores | Star-quad | Complete shielding | Aluminium foil, Shielding braid made from copper wiring |
| Overlap of shielding braid | 85 % | Wire material | Stranded tin-plated copper wire |
| Diameter of inner sheathing | 4.05 mm | Sheathing material thickness | 0.9 mm |
| Colour sequence or wires - wire pairs | white, yellow, blue, orange | Shielding braid thickness | 0.13 mm |

IE-C5DS4VG0015MCSA25-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Electrical properties of cable

| | | | |
|-------------------------|--|--------------------------------|-------------------------|
| Category | Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B) | Loop resistance | 120 Ω/km |
| Signal propagation time | 5.3 ns/m | Test voltage: wire-wire-shield | 2000 Veff, 50 Hz, 1 min |
| Operating voltage, UL | 600 V | Operating voltage (UL rating) | 600 V |
| Transfer impedance | 20 mΩ/m at 10 MHz | Characteristic impedance | 100 ± 5 Ω at 100MHz |

Mechanical and material properties of cable

| | | | |
|--------------------------------|--|---------------------------------|----------------------|
| Halogen | Yes | Min. bending radius, repetitive | 7.5 x cable diameter |
| Min. bending radius, once only | 3.5 *diameter | Abrasion resistance | good |
| Resistance to spread of flame | in accordance with IEC 60332-1 / UL 1685 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002599 | ETIM 9.0 | EC002599 |
| ETIM 10.0 | EC002599 | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 | | |