


## RS VERT 6P 12X6 S

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Distributor module with 6 voltage potentials (P1,P2,P3,P4,P5,P6) in 12P1,12P2,12P3 ,12P4,12P5 and 12P6 for tension-clamp or screw connection.

### General ordering data

Version	Interface, RS VERT, 6 P, Screw connection
Order No.	<a href="#">1128120000</a>
Type	RS VERT 6P 12X6 S
GTIN (EAN)	4032248909582
Qty.	1 items

## RS VERT 6P 12X6 S

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UR)	E141197

## Dimensions and weights

Depth	83 mm	Depth (inches)	3.2677 inch
Height	87 mm	Height (inches)	3.4252 inch
Width	122 mm	Width (inches)	4.8031 inch
Net weight	368.46 g		

## Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Rated data UL

Total operating current acc. to UL	60 A	Operating temperature UL, min.	0 °C
Operating temperature UL, max.	25 °C	Maximum current per potential connection acc. to UL	10 A
Maximum current per distributor connection acc. to UL	10 A	Rated voltage UN	300 V

## Connection data

Number of potentials	6	Distribution PCB connectors	LL3R 5.08 mm
Supply plug-in connectors	TOP 1.5GS2/180		

## Rating data

Rated voltage	250 V AC	Operating voltage	250 V AC
Maximum current per potential connection	20 A	Maximum current per distributor connection	15 A
Total operating current	120 A		

## Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	<300 V AC
Surge voltage category	III	Pollution severity level	2
Pulse voltage test (1,2/50µs)	4 kV	Insulation test voltage AC	1.2 kV

## Connection field

Min. wire cross-section, AWG	AWG 26	Type of connection	Screw connection
Sleeve with plastic collar, max.	2.5 mm <sup>2</sup>	Flexible with sleeve, min.	0.5 mm <sup>2</sup>

## RS VERT 6P 12X6 S

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Flexible with sleeve, max.	2.5 mm <sup>2</sup>	Flexible, max. H05(07) V-K	4 mm <sup>2</sup>
Flexible, min. H05(07) V-K	0.5 mm <sup>2</sup>	Solid, max. H05(07) V-U	6 mm <sup>2</sup>
Solid, min. H05(07) V-U	0.5 mm <sup>2</sup>	Stripping length	6 mm
Tightening torque, max.	0.6 Nm	Tightening torque, min.	0.5 Nm
Clamping range, max.	6 mm <sup>2</sup>	Clamping range, min.	0.13 mm <sup>2</sup>
Max. wire cross-section, AWG	AWG 12		

## Supply connection

Type of connection	Screw connection	Clamping range, min.	0.13 mm <sup>2</sup>
Clamping range, max.	6 mm <sup>2</sup>	Solid, min. H05(07) V-U	0.5 mm <sup>2</sup>
Solid, max. H05(07) V-U	6 mm <sup>2</sup>	Flexible, min. H05(07) V-K	0.5 mm <sup>2</sup>
Flexible, max. H05(07) V-K	4 mm <sup>2</sup>	Flexible with sleeve, max.	4 mm <sup>2</sup>
Flexible with sleeve, min.	0.5 mm <sup>2</sup>	Ferrule with plastic collar, max.	4 mm <sup>2</sup>
Wire cross-section, min. AWG	AWG 26	Wire cross-section, max. AWG	AWG 10
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	13 mm		

## Classifications

ETIM 8.0	EC002780	ETIM 9.0	EC002780
ETIM 10.0	EC002780	ECLASS 14.0	27-14-11-52
ECLASS 15.0	27-14-11-52		

**RS VERT 6P 12X6 S**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

