


RSM-8 PLC C SW 1CO S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Digital output interface per-relay for electrical signal transmission between the PLC and the field.

- Electrical isolation using pluggable relays.
- Integrated LED status display.
- Screw or tension clamp connection.
- The relay switchover can be carried out by the PLC or manually by a relay.
- Two available versions: compact (RSS Relais) or standard (RSS Relais).

General ordering data

| | |
|------------|--|
| Version | Interface, RSM PLC, 8 with switch, RSS, Screw connection |
| Order No. | 1128990000 |
| Type | RSM-8 PLC C SW 1CO S |
| GTIN (EAN) | 4032248910342 |
| Qty. | 1 items |

RSM-8 PLC C SW 1CO S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E141197 |

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 85 mm | Depth (inches) | 3.3464 inch |
| Height | 109 mm | Height (inches) | 4.2913 inch |
| Width | 75 mm | Width (inches) | 2.9527 inch |
| Net weight | 554.4 g | | |

Temperatures

| | | | |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -40...60 °C | Operating temperature | -25...50 °C |
|---------------------|-------------|-----------------------|-------------|

Environmental Product Compliance

| | |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 71d9bdc4-a0b5-4af0-93bd-2ad4e523fb14 |

Rated data UL

| | | | |
|---|-------|--------------------------------|--------|
| Rated current I _N | 13 mA | Operating temperature UL, min. | -25 °C |
| Operating temperature UL, max. | 50 °C | Rated voltage DC UN (supply) | 24 V |
| Rated current (supply) | 2 A | Rated current fuse (supply) | 2.5 A |
| Rated voltage DC UN (input) | 24 V | Rated voltage AC UN (output) | 250 V |
| Rated current I _{max} (output) | 2.5 A | | |

General data

| | | | |
|------------------------------|-----------------|----------------------------------|--------|
| LED status display per relay | green | Fuse per relay | No |
| Contactors | Yes (coil side) | LED status of the supply voltage | yellow |
| Power supply fuse | 2.5 A | | |

Connection data

| | | | |
|--------------------------------|--------------|----------------------------|---|
| Number of poles (control side) | 20-pole plug | Connection supply | LL 5.08 mm |
| Connection (field side) | LL3R 5.08 mm | Connection on control side | Plug-in connector in acc. with IEC60603-13 / DIN41651 |

Rating data

| | |
|-------------------------|--------------------------------------|
| Mechanical service life | 5 x 10 ⁶ switching cycles |
|-------------------------|--------------------------------------|

Ratings data input

| | | | |
|---------------|---------------|---------------|-------|
| Input voltage | 24 V DC ± 10% | Input current | 13 mA |
| Power rating | 0.36 W | | |

RSM-8 PLC C SW 1CO S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Ratings data output

| | | | |
|----------------------------|------------|-------------------------|------------------------|
| Relay type | RSS | Type of output | Potential-free contact |
| Material of contacts | AgNi 90/10 | Rated voltage | 250 V AC |
| Max. AC continuous current | 2.5 A | Minimum contact current | 0.1 A |
| Minimum contact voltage | 5 V | | |

Insulation coordinates (EN50178)

| | | | |
|-----------------------------------|--------------|------------------------------------|-----------|
| According to | DIN EN 50178 | Rated input insulation voltage | <50 V AC |
| Rated output insulation voltage | 250 V AC | Overvoltage category input/input | II |
| Overvoltage category input/output | III | Overvoltage category output/output | II |
| Pollution severity level | 2 | Pulse voltage test (1,2/50µs) | 6 kV |
| Insulation test voltage AC | 1.2 kV | Clearance input/output | ≥ 5.5 mm |
| Clearance input/input | ≥ 0.2 mm | Clearance output/output | ≥ 1.17 mm |

Connection field

| | | | |
|----------------------------------|---------------------|----------------------------|----------------------|
| Min. wire cross-section, AWG | AWG 26 | Type of connection | Screw connection |
| Sleeve with plastic collar, max. | 2.5 mm ² | Flexible with sleeve, min. | 0.5 mm ² |
| Flexible with sleeve, max. | 2.5 mm ² | Flexible, max. H05(07) V-K | 4 mm ² |
| Flexible, min. H05(07) V-K | 0.5 mm ² | Solid, max. H05(07) V-U | 6 mm ² |
| Solid, min. H05(07) V-U | 0.5 mm ² | Stripping length | 6 mm |
| Tightening torque, max. | 0.6 Nm | Tightening torque, min. | 0.5 Nm |
| Clamping range, max. | 6 mm ² | Clamping range, min. | 0.13 mm ² |
| Max. wire cross-section, AWG | AWG 12 | | |

Supply connection

| | | | |
|------------------------------|---------------------|-----------------------------------|----------------------|
| Type of connection | Screw connection | Clamping range, min. | 0.13 mm ² |
| Clamping range, max. | 6 mm ² | Solid, min. H05(07) V-U | 0.5 mm ² |
| Solid, max. H05(07) V-U | 6 mm ² | Flexible, min. H05(07) V-K | 0.5 mm ² |
| Flexible, max. H05(07) V-K | 4 mm ² | Flexible with sleeve, max. | 2.5 mm ² |
| Flexible with sleeve, min. | 0.5 mm ² | Ferrule with plastic collar, max. | 2.5 mm ² |
| Wire cross-section, min. AWG | AWG 26 | Wire cross-section, max. AWG | AWG 12 |
| Tightening torque, min. | 0.5 Nm | Tightening torque, max. | 0.6 Nm |
| Stripping length | 6 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002780 | ETIM 9.0 | EC002780 |
| ETIM 10.0 | EC002780 | ECLASS 14.0 | 27-14-11-52 |
| ECLASS 15.0 | 27-14-11-52 | | |

RSM-8 PLC C SW 1CO S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

