


RS ELCO 56/54LM S**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

ELCO contacts inserts are used in electrical power plants, refineries and a variety of process applications – wherever stable and reliable signal transmission is required. The ELCO connector features both a reliable connection system and a high signal capacity.

The line of RS ELCO interfaces and pre-assembled PAC ELCO cables is a specially designed solution for these requirements.

General ordering data

| | |
|------------|---|
| Version | Interface, RS ELCO, ELCO plug-in connector, 54, LP2N 5.08mm |
| Order No. | 1126750000 |
| Type | RS ELCO 56/54LM S |
| GTIN (EAN) | 403224890827 1 |
| Qty. | 1 items |

RS ELCO 56/54LM S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E141197 |

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 60 mm | Depth (inches) | 2.3622 inch |
| Height | 70 mm | Height (inches) | 2.7559 inch |
| Width | 155 mm | Width (inches) | 6.1024 inch |
| Net weight | 280 g | | |

Temperatures

| | | | |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -40...60 °C | Operating temperature | -25...50 °C |
|---------------------|-------------|-----------------------|-------------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 7b5ffb72-271d-4c73-8b09-bd0aaee3697a |

Rated data UL

| | | | |
|--------------------------------|-------|--------------------------------|---------------------|
| Rated current IN | 1 A | Operating temperature UL, min. | -25 °C |
| Operating temperature UL, max. | 50 °C | Rated voltage UN | 150 V AC / 200 V DC |

Connection Data

| | | | |
|--------------------------------|------------------------|---------------------------------|-----------------------|
| Number of poles (control side) | 56-pole plug | Polarity hardware codification | 1 |
| Connection (field side) | LP2N 5.08mm | Contact material (control side) | Phosphor bronze alloy |
| Connection on control side | ELCO plug-in connector | | |

Rating data

| | | | |
|-------------------------|---------------------|------------------------------|-------|
| Rated voltage | 150 V AC / 200 V DC | Rated current per connection | 1.5 A |
| Total operating current | 81 A | | |

Insulation coordination (EN50178)

| | | | |
|-------------------------------|--------------|----------------------------|-----------|
| According to | DIN EN 50178 | Rated insulation voltage | <150 V AC |
| Surge voltage category | II | Pollution severity level | 2 |
| Pulse voltage test (1,2/50µs) | 2.5 kV | Insulation test voltage AC | 0.8 kV |

Connection field

| | | | |
|----------------------------------|---------------------|----------------------------|---------------------|
| Min. wire cross-section, AWG | AWG 26 | Type of connection | Screw connection |
| Sleeve with plastic collar, max. | 2.5 mm ² | Flexible with sleeve, min. | 0.5 mm ² |
| Flexible with sleeve, max. | 2.5 mm ² | Flexible, max. H05(07) V-K | 4 mm ² |
| Flexible, min. H05(07) V-K | 0.5 mm ² | Solid, max. H05(07) V-U | 6 mm ² |

RS ELCO 56/54LM S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | | |
|------------------------------|---------------------|-------------------------|---------------------|
| Solid, min. H05(07) V-U | 0.5 mm ² | Stripping length | 6 mm |
| Tightening torque, max. | 0.6 Nm | Tightening torque, min. | 0.5 Nm |
| Clamping range, max. | 6 mm ² | Clamping range, min. | 0.5 mm ² |
| Max. wire cross-section, AWG | AWG 12 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002780 | ETIM 9.0 | EC002780 |
| ETIM 10.0 | EC002780 | ECLASS 14.0 | 27-14-11-52 |
| ECLASS 15.0 | 27-14-11-52 | | |

Drawings

