

HDC 04A CSB FEMALE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



A heavy-duty connector consists of a connector insert and its protective housing. The insert is therefore the heart of the heavy-duty connector. It is responsible for electrical functioning. Connector inserts from Weidmüller are made from high-quality insulation materials, which allow secure transmission of high voltages in a tight space. Moreover, we use only a single type of plastic in our entire product line. This plastic is UL listed, and suitable for railway applications. This allows unlimited worldwide use of the RockStar® connector.

General ordering data

Version	HDC insert, Female, 0 A, Number of poles: 1, Crimp connection, Installation size: 1
Order No.	1137760000
Type	HDC 04A CSB FEMALE
GTIN (EAN)	4032248919659
Qty.	1 items

HDC 04A CSB FEMALE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	21 mm	Depth (inches)	0.8268 inch
Height	27 mm	Height (inches)	1.063 inch
Width	21 mm	Width (inches)	0.8268 inch
Net weight	7.2 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

Dimensions

Width	21 mm	Height of socket	27 mm
-------	-------	------------------	-------

General data

Number of poles	1	Plugging cycles, silver	≥ 500
Plugging cycles, gold	≥ 500	Type of connection	Crimp connection
Installation size	1	UL 94 flammability rating	V-0
Colour	beige	Insulation resistance	1010 Ω
Insulating material	PC glass-fibre reinforced (UL-listed and railway-certified)	Insulating material group	IIIa
Surface finish	Miscellaneous	Type	Female
Pollution severity	3	Basic material	Polycarbonate
Series	ConCept module	Rated current (DIN EN 61984)	0 A
Free from halogens	true	Low smoke acc. DIN EN 45545-2	Yes
BG	1		

Connection data PE

Connection type PE	Miscellaneous
--------------------	---------------

Version

Wire connection cross section AWG, max.	AWG 12	Type of connection	Crimp connection
Installation size	1	Wire connection cross section AWG, min.	AWG 26
Conductor cross-section, max.	4 mm ²	Conductor cross-section, min.	0.14 mm ²
Surface finish	Miscellaneous	Basic material	Polycarbonate
BG	1		

HDC 04A CSB FEMALE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-05
ECLASS 15.0	27-44-02-05		