


RS VERT 6P 12X6 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Distributor module with 6 voltage potentials (P1,P2,P3,P4,P5,P6) in 12P1,12P2,12P3 ,12P4,12P5 and 12P6 for tension-clamp or screw connection.

General ordering data

| | |
|------------|---|
| Version | Interface, RS VERT, 6 P, Screw connection |
| Order No. | 1128120000 |
| Type | RS VERT 6P 12X6 S |
| GTIN (EAN) | 4032248909582 |
| Qty. | 1 items |

RS VERT 6P 12X6 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-----------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E141197 |

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 83 mm | Depth (inches) | 3.2677 inch |
| Height | 87 mm | Height (inches) | 3.4252 inch |
| Width | 122 mm | Width (inches) | 4.8031 inch |
| Net weight | 368.46 g | | |

Temperatures

| | | | |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -40...60 °C | Operating temperature | -25...50 °C |
|---------------------|-------------|-----------------------|-------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Rated data UL

| | | | |
|---|-------|---|-------|
| Total operating current acc. to UL | 60 A | Operating temperature UL, min. | 0 °C |
| Operating temperature UL, max. | 25 °C | Maximum current per potential connection acc. to UL | 10 A |
| Maximum current per distributor connection acc. to UL | 10 A | Rated voltage UN | 300 V |

Connection data

| | | | |
|---------------------------|----------------|-----------------------------|--------------|
| Number of potentials | 6 | Distribution PCB connectors | LL3R 5.08 mm |
| Supply plug-in connectors | TOP 1.5GS2/180 | | |

Rating data

| | | | |
|--|----------|--|----------|
| Rated voltage | 250 V AC | Operating voltage | 250 V AC |
| Maximum current per potential connection | 20 A | Maximum current per distributor connection | 15 A |
| Total operating current | 120 A | | |

Insulation coordination (EN50178)

| | | | |
|-------------------------------|--------------|----------------------------|-----------|
| According to | DIN EN 50178 | Rated insulation voltage | <300 V AC |
| Surge voltage category | III | Pollution severity level | 2 |
| Pulse voltage test (1,2/50µs) | 4 kV | Insulation test voltage AC | 1.2 kV |

Connection field

| | | | |
|----------------------------------|---------------------|----------------------------|---------------------|
| Min. wire cross-section, AWG | AWG 26 | Type of connection | Screw connection |
| Sleeve with plastic collar, max. | 2.5 mm ² | Flexible with sleeve, min. | 0.5 mm ² |

RS VERT 6P 12X6 S

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | | |
|------------------------------|---------------------|----------------------------|----------------------|
| Flexible with sleeve, max. | 2.5 mm ² | Flexible, max. H05(07) V-K | 4 mm ² |
| Flexible, min. H05(07) V-K | 0.5 mm ² | Solid, max. H05(07) V-U | 6 mm ² |
| Solid, min. H05(07) V-U | 0.5 mm ² | Stripping length | 6 mm |
| Tightening torque, max. | 0.6 Nm | Tightening torque, min. | 0.5 Nm |
| Clamping range, max. | 6 mm ² | Clamping range, min. | 0.13 mm ² |
| Max. wire cross-section, AWG | AWG 12 | | |

Supply connection

| | | | |
|------------------------------|---------------------|-----------------------------------|----------------------|
| Type of connection | Screw connection | Clamping range, min. | 0.13 mm ² |
| Clamping range, max. | 6 mm ² | Solid, min. H05(07) V-U | 0.5 mm ² |
| Solid, max. H05(07) V-U | 6 mm ² | Flexible, min. H05(07) V-K | 0.5 mm ² |
| Flexible, max. H05(07) V-K | 4 mm ² | Flexible with sleeve, max. | 4 mm ² |
| Flexible with sleeve, min. | 0.5 mm ² | Ferrule with plastic collar, max. | 4 mm ² |
| Wire cross-section, min. AWG | AWG 26 | Wire cross-section, max. AWG | AWG 10 |
| Tightening torque, min. | 0.5 Nm | Tightening torque, max. | 0.6 Nm |
| Stripping length | 13 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002780 | ETIM 9.0 | EC002780 |
| ETIM 10.0 | EC002780 | ECLASS 14.0 | 27-14-11-52 |
| ECLASS 15.0 | 27-14-11-52 | | |

RS VERT 6P 12X6 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

