


RS VERT 6P 12X6 Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Distributor module with 6 voltage potentials (P1,P2,P3,P4,P5,P6) in 12P1,12P2,12P3 ,12P4,12P5 and 12P6 for tension-clamp or screw connection.

General ordering data

Version	Interface, RS VERT, 6 P, Tension-clamp connection
Order No.	1128130000
Type	RS VERT 6P 12X6 Z
GTIN (EAN)	4032248909667
Qty.	1 items

RS VERT 6P 12X6 Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E141197

Dimensions and weights

Depth	75 mm	Depth (inches)	2.9527 inch
Height	87 mm	Height (inches)	3.4252 inch
Width	122 mm	Width (inches)	4.8031 inch
Net weight	264 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Rated data UL

Total operating current acc. to UL	60 A	Operating temperature UL, min.	0 °C
Operating temperature UL, max.	25 °C	Maximum current per potential connection acc. to UL	10 A
Maximum current per distributor connection acc. to UL	10 A	Rated voltage UN	300 V

Connection data

Number of potentials	6	Distribution PCB connectors	LM3NZF 5.08mm
Supply plug-in connectors	TOP 1.5GS2/180		

Rating data

Rated voltage	250 V AC	Operating voltage	250 V AC
Maximum current per potential connection	20 A	Maximum current per distributor connection	15 A
Total operating current	120 A		

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	<300 V AC
Surge voltage category	III	Pollution severity level	2
Pulse voltage test (1,2/50µs)	4 kV	Insulation test voltage AC	1.2 kV

Connection field

Min. wire cross-section, AWG	AWG 24	Type of connection	Tension-clamp connection
Sleeve with plastic collar, max.	1.5 mm ²	Flexible with sleeve, min.	0.25 mm ²

RS VERT 6P 12X6 Z

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Flexible with sleeve, max.	1.5 mm ²	Flexible, max. H05(07) V-K	1.5 mm ²
Flexible, min. H05(07) V-K	0.2 mm ²	Solid, max. H05(07) V-U	2.5 mm ²
Solid, min. H05(07) V-U	0.2 mm ²	Stripping length	7.5 mm
Clamping range, max.	2.5 mm ²	Clamping range, min.	0.13 mm ²
Max. wire cross-section, AWG	AWG 14		

Supply connection

Type of connection	Screw connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²	Solid, min. H05(07) V-U	0.5 mm ²
Solid, max. H05(07) V-U	6 mm ²	Flexible, min. H05(07) V-K	0.5 mm ²
Flexible, max. H05(07) V-K	4 mm ²	Flexible with sleeve, max.	4 mm ²
Flexible with sleeve, min.	0.5 mm ²	Ferrule with plastic collar, max.	4 mm ²
Wire cross-section, min. AWG	AWG 26	Wire cross-section, max. AWG	AWG 10
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.6 Nm
Stripping length	13 mm		

Classifications

ETIM 8.0	EC002780	ETIM 9.0	EC002780
ETIM 10.0	EC002780	ECLASS 14.0	27-14-11-52
ECLASS 15.0	27-14-11-52		

RS VERT 6P 12X6 Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

