

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com













1

Overvoltage coupling along the conductor path may disturb or destroy sensitive signal inputs. It is important to provide protection in the immediate vicinity of I&C devices. Weidmüller's broad product range for the I&C sector offers products in a 2-piece, pluggable design and modular terminals for tension clamp or screw connection. These products are suitable for both binary and analogue signals. Weidmüller also offers other designs with integrated components such as gas discharge tubes or varistors. VARITECTOR stands for flexible and variable surge protection by Weidmüller, tested according to product standard IEC61643-21. The VARITECTOR series can be used in applications according to IEC 61643-22 / VDE 0845-3 for classes C1, C2, C3 and D1. The VARITECTOR SPC, SSC and MCZ OVP product families optimally combine electrical and mechanical properties. Size and easy handling play an important role. This surge protection is suited for confined spaces in industrical and process automation as well as in building automation applications.

General ordering data

Version	Surge protection for instrumentation and control,
	Surge protection for measurement and control,
	UP(L/N-PE) 150 V
Order No.	<u>1139710000</u>
Туре	VSSC6 RTD
GTIN (EAN)	4032248921713
Qty.	10 items



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Approvals	3
-----------	---

Approvals	C CSAEX COVE	UL)

ROHS	Conform
UL File Number Search	<u>UL Website</u>
Certificate No. (UL)	E311081

Dimensions and weights

Depth	81 mm	Depth (inches)	3.189 inch
Height	88.5 mm	Height (inches)	3.4842 inch
Width	6.2 mm	Width (inches)	0.2441 inch
Net weight	43.8 g		

Temperatures

Storage temperature	-40 °C80 °C	Operating temperature	-40 °C70 °C
Humidity	596 %		

Probability of failure

SIL in compliance with IEC 61508	3	MTTF	1812 a
SFF	94.05 %	λges	63
PFH in 1*10-9 per hour	3.75		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	71e97bb7-979f-4330-94c0-20c629bb05e3

Rated data UL

Certificate No. (UL)	E311081	

CSA protection data


Gas group D	IIA	Gas groups A, B	IIC	
Input-current, max. II	300 mA	Gas group C	IIB	
Internal inductance, max. LI	0 μΗ	Internal capacity, max. Cl	9 nF	
Input voltage, max. Ui	5 V			

General data

Optical function display	No	Segment	Measurement - Monitoring - Setting
Version	Surge protection for measurement and control	Design	Terminal
UL 94 flammability rating	V-0	Colour	black
Protection degree	IP20	Mounting rail	TS 35

Creation date 30.11.2025 02:49:17 MEZ

Catalogue status / Drawings 2





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Surge voltage category	III	Pollution severity	2
Rated data IEC / EN			
Number of poles	1	Rated voltage (DC)	1 V
Rated current IN	300 mA	Protection level, UP wire - wire	15 V
Protection level UP (typ.)	150 V	Voltage type	DC
Volume resistance	1.8 Ω 10 %	Standards	IEC 61643-21
Lightning test current limp (10/350 μs)		Discharge current, max. (8/20 µs)	10 kA
Requirements category acc. to IEC 61643-21	C2, C3, D1	Insertion loss	117.08 MHz
Max. continuous voltage, Uc (DC)	5 V	Surge current-carrying capacity D1	0.5 kA 10/350 μs
Surge current-carrying capacity C3	10 A 10/1000 μs	Pulse-reset capacity	≤ 10 ms
Overload - failure mode	Modus 2	Discharge current In (8/20µs) wire-wire	
Discharge current In (8/20µs) wire-PE	2.5 kA	Discharge current Imax (8/20µs) wire-F	
Discharge current Imax (8/20µs) wire- wire	5 kA	Surge current-carrying capacity C2	2.5 kA 8/20 µs 5 kV 1.2/50 µs
Further details of approvals			
GOST certificate	GOST-Zertifikat -		
	PDF/7950_n1-n4.pdf (application/pdf)		
Connection data			
Stripping length	10 mm	Type of connection	Screw connection
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.8 Nm
Clamping range, min.	0.5 mm ²	Clamping range, max.	4 mm ²
Wire cross-section, solid, min.	0.5 mm ²	Wire cross-section, solid, max.	6 mm ²
Conductor cross-section, flexible, AEH (DIN 46228-1), min.	0.5 mm ²	Conductor cross-section, flexible, AEH (DIN 46228-1), max.	4 mm ²
Connection cross-section, stranded, mir	n. 0.5 mm²	Connection cross-section, stranded, max.	4 mm²
Electrical data			
Voltage type	DC		
General data			
Jeneral data			
Number of poles	1	Protection degree	IP20
Colour	black		
Ratings IECEx/ATEX/cUL			
cUL certificate	cUL Certificate - pdf/ VSSC.PDF (application/ pdf)		
Important note			
Product information	Mode 2: State where the ve	oltage-limiting part of the SPD was short-cir	cuited due to a very lo

Creation date 30.11.2025 02:49:17 MEZ

Catalogue status / Drawings





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Technical data

Classifications

ETIM 7.0	EC000943	ETIM 8.0	EC000943
ETIM 9.0	EC000943	ETIM 10.0	EC000943
ECLASS 12.0	27-17-15-01	ECLASS 13.0	27-17-15-01
ECLASS 14.0	27-17-15-01	ECLASS 15.0	27-17-15-01

Tender specification sheets

Long specification	Surge protection in a one piece, 6.2 mm wide DIN rail module for a PT100 signal circuit with 12 V DC, 3-wire technology. A 3-wire signal with max. 0.3A can be protected here. When the terminal is fitted, a simultaneous electrically conducting contact is made between the mounting rail (earth) and the reference potential (ground) of the protection circuit in the terminal. Optical identification of the terminal based on the type of protected switching and the voltage level. The terminal can be labelled or marked.	Short specification	Surge protection in a one piece, 6.2 mm wide DIN rail module for a PT100 signal circuit with 3-wire technology. Version: 5V DC



Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

Drawings



Similar to illustration



Circuit diagram

