



**SV 7.62IT/04/90MF4 3.5SN BK BX**
**Weidmüller Interface GmbH & Co. KG**

 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)


90° male header with soldered flange fastening with 7.62 pitch for 400 V IT power networks according to IEC 61800-5-1.

UL approval as per UL840 600 V.

Meets the extended requirements on 5.5 mm touch safety for IT power networks as per IEC 61800-5-1 for 400 V to earth when combined with female header BVZ 7.62 IT...

Without a female header, the mating profile guarantees minimum touch safety of >3 mm with 20 N pressure on the test finger.

The automatically locking middle flange which can optionally also be screwed, reduces space requirements by one pitch width in comparison with conventional solutions.

On request: available with screw flange or without flange.

**General ordering data**

|              |                                                                                                                                                                            |
|--------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version      | PCB plug-in connector, male header, closed side, Middle flange, THT solder connection, 7.62 mm, Number of poles: 4, 90°, Solder pin length (l): 3.5 mm, tinned, black, Box |
| Order No.    | <a href="#">1156590000</a>                                                                                                                                                 |
| Type         | SV 7.62IT/04/90MF4 3.5SN BK BX                                                                                                                                             |
| GTIN (EAN)   | 4032248943401                                                                                                                                                              |
| Qty.         | 48 items                                                                                                                                                                   |
| Product data | IEC: 1000 V / 41 A<br>UL: 300 V / 40.5 A                                                                                                                                   |
| Packaging    | Box                                                                                                                                                                        |

## SV 7.62IT/04/90MF4 3.5SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E60693

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 28.3 mm | Depth (inches)  | 1.1142 inch |
| Height     | 14.9 mm | Height (inches) | 0.5866 inch |
| Width      | 38.1 mm | Width (inches)  | 1.5 inch    |
| Net weight | 8.37 g  |                 |             |

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## System specifications

|                                            |                                         |                                              |                                            |
|--------------------------------------------|-----------------------------------------|----------------------------------------------|--------------------------------------------|
| Product family                             | OMNIMATE Power - series<br>BV/SV 7.62IT | Type of connection                           | Board connection                           |
| Mounting onto the PCB                      | THT solder connection                   | Pitch in mm (P)                              | 7.62 mm                                    |
| Pitch in inches (P)                        | 0.300 "                                 | Outgoing elbow                               | 90°                                        |
| Number of poles                            | 4                                       | Number of solder pins per pole               | 2                                          |
| Solder pin length (l)                      | 3.5 mm                                  | Solder pin length tolerance                  | +0.1 / -0.3 mm                             |
| Solder pin dimensions                      | 0.8 x 1.0 mm                            | Solder eyelet hole diameter (D)              | 1.3 mm                                     |
| Solder eyelet hole diameter tolerance (D)  | + 0.1 mm                                | L1 in mm                                     | 30.48 mm                                   |
| L1 in inches                               | 1.200 "                                 | Number of rows                               | 1                                          |
| Pin series quantity                        | 2                                       | Touch-safe protection acc. to DIN VDE 57 106 | Touch-safe above the printed circuit board |
| Touch-safe protection acc. to DIN VDE 0470 | IP 20                                   | Protection degree                            | IP20                                       |
| Volume resistance                          | 2.00 mΩ                                 | Can be coded                                 | Yes                                        |

## Material data

|                                       |                                |                                       |                                |
|---------------------------------------|--------------------------------|---------------------------------------|--------------------------------|
| Insulating material                   | PA GF                          | Colour                                | black                          |
| Colour chart (similar)                | RAL 9011                       | Insulating material group             | II                             |
| Comparative Tracking Index (CTI)      | ≥ 500                          | Moisture Level (MSL)                  |                                |
| UL 94 flammability rating             | V-0                            | Contact material                      | Copper alloy                   |
| Contact surface                       | tinned                         | Layer structure of solder connection  | 1...3 µm Ni / 4...6 µm Sn matt |
| Layer structure of plug contact       | 1...3 µm Ni / 4...6 µm Sn matt | Storage temperature, min.             | -40 °C                         |
| Storage temperature, max.             | 70 °C                          | Operating temperature, min.           | -50 °C                         |
| Operating temperature, max.           | 130 °C                         | Temperature range, installation, min. | -25 °C                         |
| Temperature range, installation, max. | 130 °C                         |                                       |                                |

## SV 7.62IT/04/90MF4 3.5SN BK BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Rated data acc. to IEC

|                                                                           |                        |                                                                       |                   |
|---------------------------------------------------------------------------|------------------------|-----------------------------------------------------------------------|-------------------|
| tested acc. to standard                                                   | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C)                         | 41 A              |
| Rated current, max. number of poles (Tu=20°C)                             | 41 A                   | Rated current, min. number of poles (Tu=40°C)                         | 41 A              |
| Rated current, max. number of poles (Tu=40°C)                             | 41 A                   | Rated voltage for surge voltage class / pollution degree II/2         | 1000 V            |
| Rated voltage for surge voltage class / pollution degree III/2            | 630 V                  | Rated voltage for surge voltage class / pollution degree III/3        | 630 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 6 kV                   | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 6 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 6 kV                   | Short-time withstand current resistance                               | 3 x 1s with 420 A |
| Creepage distance, min.                                                   | 9.6 mm                 | Clearance, min.                                                       | 6.9 mm            |

## Rated data acc. to CSA

|                                   |                                                                        |                                   |                 |
|-----------------------------------|------------------------------------------------------------------------|-----------------------------------|-----------------|
| Institute (CSA)                   | CSA                                                                    | Certificate No. (CSA)             | 200039-112 1690 |
| Rated voltage (Use group B / CSA) | 300 V                                                                  | Rated voltage (Use group C / CSA) | 300 V           |
| Rated voltage (Use group D / CSA) | 600 V                                                                  | Rated current (Use group B / CSA) | 35 A            |
| Rated current (Use group C / CSA) | 35 A                                                                   | Rated current (Use group D / CSA) | 5 A             |
| Reference to approval values      | Specifications are maximum values, details - see approval certificate. |                                   |                 |

## Rated data acc. to UL 1059

|                                       |                                                                        |                                       |        |
|---------------------------------------|------------------------------------------------------------------------|---------------------------------------|--------|
| Institute (cURus)                     | CURUS                                                                  | Certificate No. (cURus)               | E60693 |
| Rated voltage (Use group B / UL 1059) | 300 V                                                                  | Rated voltage (Use group C / UL 1059) | 300 V  |
| Rated voltage (Use group D / UL 1059) | 600 V                                                                  | Rated voltage (Use group F / UL 1059) | 744 V  |
| Rated current (Use group B / UL 1059) | 40.5 A                                                                 | Rated current (Use group C / UL 1059) | 40.5 A |
| Rated current (Use group D / UL 1059) | 5 A                                                                    | Rated current (Use group F / UL 1059) | 40.5 A |
| Creepage distance, min.               | 9.6 mm                                                                 | Clearance distance, min.              | 6.9 mm |
| Reference to approval values          | Specifications are maximum values, details - see approval certificate. |                                       |        |

## Packing

|           |           |            |           |
|-----------|-----------|------------|-----------|
| Packaging | Box       | VPE length | 350.00 mm |
| VPE width | 136.00 mm | VPE height | 41.00 mm  |

## Important note

|                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |  |  |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.                                                                                                                                                                                                                                                                                                                                                                                                        |  |  |
| Notes          | <ul style="list-style-type: none"> <li>• Additional variants on request</li> <li>• Rated current related to rated cross-section &amp; min. No. of poles.</li> <li>• P on drawing = pitch</li> <li>• Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.</li> <li>• In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load</li> <li>• Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul> |  |  |

**SV 7.62IT/04/90MF4 3.5SN BK BX****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002637    | ETIM 9.0    | EC002637    |
| ETIM 10.0   | EC002637    | ECLASS 14.0 | 27-46-02-01 |
| ECLASS 15.0 | 27-46-02-01 |             |             |

