

THM ET S7 50/12.5 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM ET S7 non-adhesive, roll-packaged labels are used to label the SIMATIC ET 200S and S7-modules from Siemens.

The M-Print® PRO software can be used to individually print the THM ET S7 labels with a THM printer. Labels can be easily separated. The THM MultiMark printer ensures highly-resistant printing.

General ordering data

Version	THM, Device markers, 50 x 12.5 mm, Siemens, yellow
Order No.	1161810000
Type	THM ET S7 50/12.5 GE
GTIN (EAN)	4032248950690
Qty.	1 items

THM ET S7 50/12.5 GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	50 mm	Height (inches)	1.9685 inch
Width	12.5 mm	Width (inches)	0.4921 inch
Net weight	570 g		

Temperatures

Operating temperature range -50...100 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Material colour according to resistance code	4		
Printing method	Thermal transfer		
Version	halogen-free		
Width	12.5 mm		
UL 94 flammability rating	HB		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-50 °C		
Colour	yellow		
Halogen	No		
Basic material	Polypropylene		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Approval acc. to UL 969	No		
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS		
Number of markers per combination	1 Label reel = Device markers		
Operating temperature range	-50...100 °C		
Application/manufacturer	Siemens		
Number per roll	2000		

Device markers

Halogen No

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

