


SR-SMD 4.50/05/90 AU BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The integrated rail bus for the modular electronics housing system

When supplying, connecting or distributing within modular applications, the rail bus can replace the tedious individual wiring process with a flexible and uninterrupted system-wide solution.

The system bus is securely integrated within the 35-mm standard mounting rail. The SMD-bus contact block can be reflow-soldered so that it can be completely automatically processed during the component assembly. The resistant, gold-plated contact surfaces ensure a permanent and reliable contact for all housing widths.

- Unlimited scalability The integrated connection solution covers all system widths: from the 6-mm slice to the 67-mm large-area housing.
- Easy to service during installation It's easy to replace a module, even in existing modules groups – without any influence on the neighbouring modules.
- Universal integration The uninterrupted system bus is securely integrated within the 35-mm standard mounting rail.
- Maximum availability Five fully-galvanized and partially gold-plated twin-arched contacts are used to establish a permanent contact to the rail bus. THR solder flanges ensure that the connection to the circuit board is stable.

General ordering data

| | |
|--------------|--|
| Version | PCB plug-in connector, Bus-contact block for CH20M6, THT/THR solder connection, Number of poles: 5, 180°, Gold-plated, black |
| Order No. | 1155840000 |
| Type | SR-SMD 4.50/05/90 AU BK BX |
| GTIN (EAN) | 4032248942534 |
| Qty. | 78 items |
| Product data | IEC: 160 V UL: 300 V / 5 A |
| Packaging | Box |

SR-SMD 4.50/05/90 AU BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform
UL File Number Search [UL Website](#)
Certificate No. (cURus) E60693

Dimensions and weights

| | | | |
|--------|---------|-----------------|-------------|
| Depth | 16.3 mm | Depth (inches) | 0.6417 inch |
| Height | 24 mm | Height (inches) | 0.9449 inch |
| Width | 7.4 mm | Width (inches) | 0.2913 inch |
| Length | 0 mm | Net weight | 2 g |

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Material data

| | | | |
|---------------------------------------|----------------|---------------------------------------|-------------|
| Insulating material | LCP | Colour | black |
| Colour chart (similar) | RAL 9011 | Insulating material group | IIIa |
| Comparative Tracking Index (CTI) | 175 ≤ CTI <400 | Insulation resistance | ≥ 108 Ω |
| Moisture Level (MSL) | 1 | Contact surface | Gold-plated |
| Storage temperature, min. | -40 °C | Storage temperature, max. | 70 °C |
| Operating temperature, min. | -50 °C | Operating temperature, max. | 100 °C |
| Temperature range, installation, min. | -30 °C | Temperature range, installation, max. | 100 °C |

Rated data acc. to IEC

| | | | |
|--|------------------------|--|--------------------|
| tested acc. to standard | IEC 60664-1, IEC 61984 | Rated current, max. number of poles (Tu=40°C) | 3.6 A |
| Rated voltage for surge voltage class / pollution degree II/2 | 160 V | Rated voltage for surge voltage class / pollution degree III/2 | 100 V |
| Rated voltage for surge voltage class / pollution degree III/3 | 63 V | Short-time withstand current resistance | 3 x 1s with 14.5 A |
| Rated impulse voltage for surge voltage class/ pollution degree II/3 | 1.5 kV | Creepage distance, min. | 3.2 mm |
| Clearance, min. | 2.3 mm | | |

Rated data acc. to UL 1059

| | | | |
|---------------------------------------|--|---------------------------------------|--------|
| Institute (cURus) | CURUS | Certificate No. (cURus) | E60693 |
| Rated voltage (Use group B / UL 1059) | 300 V | Rated voltage (Use group C / UL 1059) | 50 V |
| Rated voltage (Use group D / UL 1059) | 50 V | Rated current (Use group B / UL 1059) | 5 A |
| Rated current (Use group C / UL 1059) | 5 A | Rated current (Use group D / UL 1059) | 5 A |
| Reference to approval values | Specifications are maximum values, details - see approval certificate. | | |

Material data

| | | | |
|----------------------------------|----------------|---------------------------|---------|
| Insulating material | LCP | Insulating material group | IIIa |
| Surface finish | gold | Basic material | Plastic |
| Comparative Tracking Index (CTI) | 175 ≤ CTI <400 | | |

SR-SMD 4.50/05/90 AU BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**General data**

| | | | |
|------------------------|----------|-------------------|-------------------------|
| Colour | black | Protection degree | IP20 in installed state |
| Colour chart (similar) | RAL 9011 | | |

Important note

| | |
|----------------|--|
| IPC conformity | Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request. |
|----------------|--|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001031 | ETIM 9.0 | EC001031 |
| ETIM 10.0 | EC001031 | ECLASS 14.0 | 27-18-27-92 |
| ECLASS 15.0 | 27-18-27-92 | | |

SR-SMD 4.50/05/90 AU BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings