


**SAI-M23-SE-17****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Pinning**

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

**General ordering data**

Version	Sensor/Actuator plug-in connector, Insert
Order No.	<a href="#">1170100000</a>
Type	SAI-M23-SE-17
GTIN (EAN)	4032248962181
Qty.	1 items

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (UR)	E344862

**Dimensions and weights**

Net weight	3 g
------------	-----

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Technical data customisable plug-in connectors**


Number of poles	17	Coding	none
Type of connection	Crimp connection	Housing main material	Thermoplastic polyamide PA 6, PBT
Nominal voltage	160 V	Nominal current	8 A
Plugging cycles	> 1000	Pollution severity	3
Rated current	1 mm contact = 8 A	Gender of contact	Male
Coding possibilities for M23 signal inserts	H-coded, N-coded, S-coded, X-coded, Y-coded, Z-coded		

**Classifications**


ETIM 8.0	EC003557	ETIM 9.0	EC003557
ETIM 10.0	EC003557	ECLASS 14.0	27-44-02-23
ECLASS 15.0	27-44-02-23		

**Drawings**

**Pinning**



**Dimensioned drawing**



**Technical data**

Number of positions	6	7	9		12	16	17	19		
Number of contacts	6	7	8	1	12	16	17	16	3	
Contact-ø	mm		2	2	1	2	1	1	1	1.5

