

## E1W/63/M63-WM

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



E1W type cable glands are suitable for SWA steel wired armor cable, E1W type glands maintain flameproof Ex d and Increased Safety Ex e explosion protection. And the armor clamping provides an electrical bond between the cable armor and the glands.

### General ordering data

Version	E1W (Klippon double seal SWA armored Ex e/d cable gland), Cable glands, straight, M 63 x 1.5, 19 mm, Single-wire armouring, 2.5 - 2.5 mm, OD min. 58 - OD max. 66 mm, ID min. 49.50 - ID max. 56.00 mm, Brass, nickel-plated
Order No.	<a href="#">1184750000</a>
Type	E1W/63/M63-WM
GTIN (EAN)	4050118074796
Qty.	4 items
Delivery status	This article will no longer be available in the future.
Available until	2024-08-31T00:00:00+02:00

**E1W/63/M63-WM**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Height	77.5 mm	Height (inches)	3.0512 inch
Width	88 mm	Width (inches)	3.4646 inch
Length	96.5 mm	Length (inches)	3.7992 inch
Net weight	975.7 g		

**Temperatures**

Operating temperature -50 °C... 120 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	0d756fc1-6076-45f4-ae6d-db4288d0aefd

**Certificate numbers cable gland**

Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X	Certificate no. cable gland (CCC)	2020322313000069
Certificate No. (IECEX)	IECEXTPS16.0004X		

**General information**

Outer cable diameter, max.	66 mm	Outer cable diameter, min.	58 mm
Inner cable diameter, max.	56.00 mm	Inner cable diameter, min.	49.50 mm
O-Ring	Silicone	Tightening torque	130 Nm
Silicone	Yes	Number of wires	1
Armour, max.	2.5 mm	Armour, min.	2.5 mm
Operating temperature range, max.	120 °C	Operating temperature range, min.	-50 °C
Pitch of thread	1.5 mm	Halogen	No
Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3	AF size 1	80 mm
AF size 2	80 mm	Protection degree	IP66, IP68
Cable gland	M 63	Basic material	Brass, nickel-plated
Seal insert	Silicone	Sealing	Silicone
External thread	M 63 x 1.5	Length of thread	19 mm
Type of armouring, short term	SWA	Explosion protection type	Ex d - flameproof, Ex e - increased safety
Type of armouring	Single-wire armouring	Installation guidelines	See assembly instructions

**Technical data**

**Classifications**

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-04
ECLASS 15.0	27-14-08-04		

## E1W/63/M63-WM

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Nylon flat washer - GWDR



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	GWDR M63-W	Version	
Order No.	<a href="#">1185670000</a>		in closed state, M 63, Nylon 6
GTIN (EAN)	4064675423270		
Qty.	10 ST		

## Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	SKMU M63 MS	Version	
Order No.	<a href="#">1737050000</a>		SKMU MS (brass locknut), Locknut, M 63, 6 mm, Brass, nickel-plated
GTIN (EAN)	4008190956523		
Qty.	25 ST		