

**A2LS/40/M40-WM**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Similar to illustration**



A2L type cable glands are suitable for un-armored cable, maintains flameproof Ex d and Increased Safety Ex e explosion protection.

**General ordering data**

Version	A2L (Klippon unarmored Ex e/d cable gland), Cable glands, straight, M 40 x 1.5, 16 mm, OD min. 25.5 - OD max. 32.2 mm, Stainless steel 1.4404
Order No.	<a href="#">1185330000</a>
Type	A2LS/40/M40-WM
GTIN (EAN)	405011808055 1
Qty.	9 items

## A2LS/40/M40-WM

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Height	40.8 mm	Height (inches)	1.6063 inch
Width	55 mm	Width (inches)	2.1654 inch
Length	56.8 mm	Length (inches)	2.2362 inch
Net weight	276 g		

## Temperatures

Operating temperature -50 °C... 120 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

## Certificate numbers cable gland

Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X	Certificate no. cable gland (CCC)	2020322313000069
Certificate No. (IECEX)	IECEXTPS16.0004X		

## General information

Outer cable diameter, max.	32.2 mm	Outer cable diameter, min.	25.5 mm
O-Ring	Silicone	Tightening torque	80 Nm
Operating temperature range, max.	120 °C	Operating temperature range, min.	-50 °C
Pitch of thread	1.5 mm	Halogen	No
Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7	AF size 1	50 mm
AF size 2	50 mm	Protection degree	IP66, IP68
Cable gland	M 40	Basic material	Stainless steel 1.4404
Seal insert	Silicone	Sealing	Silicone
External thread	M 40 x 1.5	Length of thread	16 mm
Explosion protection type	Ex d - flameproof, Ex e - increased safety	Installation guidelines	See assembly instructions

## Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-04
ECLASS 15.0	27-14-08-04		