

E1WS/16/M16-WM

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



E1W type cable glands are suitable for SWA steel wired armor cable, E1W type glands maintain flameproof Ex d and Increased Safety Ex e explosion protection. And the armor clamping provides an electrical bond between the cable armor and the glands.

General ordering data

Version	E1W (Klippon double seal SWA armored Ex e/d cable gland), Cable glands, straight, M 16 x 1.5, 16 mm, Single-wire armouring, 0.9 - 0.9 mm, OD min. 8 - OD max. 13.5 mm, ID min. 4.50 - ID max. 8.70 mm, Stainless steel 1.4404
Order No.	1188840000
Type	E1WS/16/M16-WM
GTIN (EAN)	4050118085082
Qty.	24 items

E1WS/16/M16-WM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	62 mm	Height (inches)	2.4409 inch
Width	26 mm	Width (inches)	1.0236 inch
Length	78 mm	Length (inches)	3.0709 inch
Net weight	110 g		

Temperatures

Operating temperature -50 °C... 120 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
REACH SVHC No SVHC above 0.1 wt%

Certificate numbers cable gland

Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X	Certificate no. cable gland (CCC)	2020322313000069
Certificate No. (IECEX)	IECEXTPS16.0004X		

General information

Outer cable diameter, max.	13.5 mm	Outer cable diameter, min.	8 mm
Inner cable diameter, max.	8.70 mm	Inner cable diameter, min.	4.50 mm
O-Ring	Silicone	Tightening torque	18 Nm
Silicone	Yes	Number of wires	1
Armour, max.	0.9 mm	Armour, min.	0.9 mm
Operating temperature range, max.	120 °C	Operating temperature range, min.	-50 °C
Pitch of thread	1.5 mm	Halogen	No
Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3	AF size 1	24 mm
AF size 2	24 mm	Protection degree	IP66, IP68
Cable gland	M 16	Basic material	Stainless steel 1.4404
Seal insert	Silicone	Sealing	Silicone
External thread	M 16 x 1.5	Length of thread	16 mm
Type of armouring, short term	SWA	Explosion protection type	Ex d - flameproof, Ex e - increased safety
Type of armouring	Single-wire armouring	Installation guidelines	See assembly instructions

Technical data

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-04
ECLASS 15.0	27-14-08-04		