

E1WS/20/NPT1/2-WM**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmuller.com



E1W type cable glands are suitable for SWA steel wired armor cable, E1W type glands maintain flameproof Ex d and Increased Safety Ex e explosion protection. And the armor clamping provides an electrical bond between the cable armor and the glands.

General ordering data

| | |
|------------|---|
| Version | E1W (Klippon double seal SWA armored Ex e/d cable gland), Cable glands, straight, 1/2" NPT, 13.6 mm, Single-wire armouring, 0.9 - 1.25 mm, OD min. 15 - OD max. 21 mm, ID min. 10.00 - ID max. 14.00 mm, Stainless steel 1.4404 |
| Order No. | 1188960000 |
| Type | E1WS/20/NPT1/2-WM |
| GTIN (EAN) | 4050118086348 |
| Qty. | 24 items |

E1WS/20/NPT1/2-WM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Height | 62.5 mm | Height (inches) | 2.4606 inch |
| Width | 33 mm | Width (inches) | 1.2992 inch |
| Length | 78.5 mm | Length (inches) | 3.0905 inch |
| Net weight | 161 g | | |

Temperatures

Operating temperature -50 °C... 120 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Certificate numbers cable gland

| | | | |
|-------------------------------------|---|------------------------------------|--------------------|
| Identification | II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da | Certificate no. cable gland (ATEX) | TÜV IT 16ATEX 059X |
| Certificate no. cable gland (IECEX) | IECEX TPS 16.0004X | Certificate no. cable gland (CCC) | 2020322313000069 |
| Certificate No. (IECEX) | IECEXTPS 16.0004X | | |

General information

| | | | |
|-----------------------------------|---|-----------------------------------|--|
| Outer cable diameter, max. | 21 mm | Outer cable diameter, min. | 15 mm |
| Inner cable diameter, max. | 14.00 mm | Inner cable diameter, min. | 10.00 mm |
| O-Ring | Silicone | Tightening torque | 35 Nm |
| Silicone | Yes | Number of wires | 1 |
| Armour, max. | 1.25 mm | Armour, min. | 0.9 mm |
| Operating temperature range, max. | 120 °C | Operating temperature range, min. | -50 °C |
| Pitch of thread | 1.81 mm | Halogen | No |
| Standards | EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3 | AF size 1 | 30 mm |
| AF size 2 | 30 mm | Protection degree | IP66, IP68 |
| Cable gland | NPT 1/2" | Basic material | Stainless steel 1.4404 |
| Seal insert | Silicone | Sealing | Silicone |
| External thread | 1/2" NPT | Length of thread | 13.6 mm |
| Type of armouring, short term | SWA | Explosion protection type | Ex d - flameproof, Ex e - increased safety |
| Type of armouring | Single-wire armouring | Installation guidelines | See assembly instructions |

E1WS/20/NPT1/2-WM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000441 | ETIM 9.0 | EC000441 |
| ETIM 10.0 | EC000441 | ECLASS 14.0 | 27-14-08-04 |
| ECLASS 15.0 | 27-14-08-04 | | |