

## IE-C5DS4VG0057A20A20-E

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### General ordering data

|            |   |
|------------|---|
| Version    | System cable, RJ45 IP 20, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PVC, 5.7 m |
| Order No.  | <a href="#">1191010057</a>  |
| Type       | IE-C5DS4VG0057A20A20-E  |
| GTIN (EAN) | 4050118413465   |
| Qty.       | 1 items   |

## IE-C5DS4VG0057A20A20-E

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

|            |       |                 |               |
|------------|-------|-----------------|---------------|
| Length     | 5.7 m | Length (inches) | 224.4094 inch |
| Net weight | 420 g |                 |               |

### Temperatures

|                          |                |                       |                |
|--------------------------|----------------|-----------------------|----------------|
| Storage temperature      | -40 °C...80 °C | Operating temperature | -40 °C...70 °C |
| Installation temperature | -40 °C...80 °C |                       |                |

### Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

### Cable specific standards

|                                |  |                              |                          |
|--------------------------------|--|------------------------------|--------------------------|
| Standard, insulating material  | DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)                      | Standard, wire material      | DIN EN 13602 Cu-ETP-A    |
| Standard, assembly             | UL-Style 21694   | Standard, shielding material | DIN EN 13602 Cu-ETP-A..B |
| Standard, additional standards | UL-File E11901 Vol.1 Sec.12 Page 1, UL-File E116441 Vol.1 Sec.6 Page 8 |                              |                          |

### Cable structure

|                                       |  |                              |   |
|---------------------------------------|--|------------------------------|---|
| Strands                               | 7  | Sheathing colour             | green (RAL 6018)  |
| Standard designations                 | 2YY(ST)CY<br>2x2x0,75/1,5-100 LI VZN<br>GN | Cross-section                | 4*AWG 22/7 - 0.32 mm <sup>2</sup>                       |
| Shielding                             | SF/UTP                                     | Number of wires              | 4   |
| Insulation cross-section              | 1.5 mm                                     | Insulation                   | PE  |
| Sheath diameter, max.                 | 6.7 mm                                     | Sheath diameter, min.        | 6.3 mm  |
| Material sheath                       | PVC  | Filler                       | As central element                                      |
| Arrangement of wire cores             | Star-quad                                  | Complete shielding           | Aluminium foil, Shielding braid made from copper wiring |
| Overlap of shielding braid            | 85 %                                       | Wire material                | Stranded tin-plated copper wire                         |
| Diameter of inner sheathing           | 4.05 mm                                    | Sheathing material thickness | 0.9 mm  |
| Colour sequence or wires - wire pairs | white, yellow, blue, orange                | Shielding braid thickness    | 0.13 mm   |

### Electrical properties of cable

|                         |   |                                |                         |
|-------------------------|---|--------------------------------|-------------------------|
| Category                | Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B) | Loop resistance                | 120 Ω/km                |
| Signal propagation time | 5.3 ns/m                                    | Test voltage: wire-wire-shield | 2000 Veff, 50 Hz, 1 min |

## IE-C5DS4VG0057A20A20-E

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

|                       |                   |                               |                     |
|-----------------------|-------------------|-------------------------------|---------------------|
| Operating voltage, UL | 600 V             | Operating voltage (UL rating) | 600 V               |
| Transfer impedance    | 20 mΩ/m at 10 MHz | Characteristic impedance      | 100 ± 5 Ω at 100MHz |

### Mechanical and material properties of cable

|                                |  |                                 |                      |
|--------------------------------|--|---------------------------------|----------------------|
| Halogen                        | Yes                                      | Min. bending radius, repetitive | 7.5 x cable diameter |
| Min. bending radius, once only | 3.5 *diameter                            | Abrasion resistance             | good                 |
| Resistance to spread of flame  | in accordance with IEC 60332-1 / UL 1685 |                                 |                      |

### Plug

|            |  |           |  |
|------------|--|-----------|--|
| Plug right | RJ45, IP20, male contact, straight, plug, Zinc diecast, shielded | Plug left | RJ45, IP20, male contact, straight, plug, Zinc diecast, shielded |
|------------|--|-----------|--|

### Plug, left

|           |  |
|-----------|--|
| Plug left | RJ45, IP20, male contact, straight, plug, Zinc diecast, shielded |
|-----------|--|

### Plug, right

|            |  |
|------------|--|
| Plug right | RJ45, IP20, male contact, straight, plug, Zinc diecast, shielded |
|------------|--|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002599    | ETIM 9.0    | EC002599    |
| ETIM 10.0   | EC002599    | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 |             |             |