

**VGM25-SS68 11-20 BG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

**General ordering data**

Version	Heavy-duty connectors, Accessories, Cable glands, Stainless steel 1.4305 (303)
Order No.	<a href="#">1193570000</a>
Type	VGM25-SS68 11-20 BG
GTIN (EAN)	4032248976546
Qty.	50 items

## VGM25-SS68 11-20 BG

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Length	36.5 mm	Length (inches)	1.437 inch
Net weight	60.58 g		

### Temperatures

Limit temperature	-40 °C ... 130 °C
-------------------	-------------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General information

Outer cable diameter, max.	20 mm	Outer cable diameter, min.	11 mm
O-Ring	Silicone	Protection degree with GWDR	IP68
UL 94 flammability rating	V-0	Operating temperature range, max.	130 °C
Operating temperature range, min.	-40 °C	Halogen	halogen-free
Standards	EN 45545-2:2013	AF size	30 mm
Protection degree	IP68 - 15 bar	Cable gland	M 25
Basic material	Stainless steel 1.4305 (303)	External thread	M 25
Length of thread	7.5 mm		

### Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		