

**VGM25-MS68 11-20 BG****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

**General ordering data**

Version	Heavy-duty connectors, Accessories, Cable glands, Brass, nickel-plated
Order No.	<a href="#">1193600000</a>
Type	VGM25-MS68 11-20 BG
GTIN (EAN)	4032248976560
Qty.	50 items

**VGM25-MS68 11-20 BG**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Length	36.5 mm	Length (inches)	1.437 inch
Net weight	70 g		

**Temperatures**

Limit temperature -40 °C ... 130 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

**General information**

Outer cable diameter, max.	20 mm	Outer cable diameter, min.	11 mm
O-Ring	NBR	Protection degree with GWDR	IP68
UL 94 flammability rating	V-0	Operating temperature range, max.	130 °C
Operating temperature range, min.	-40 °C	Halogen	halogen-free
Standards	EN 45545-2:2013	AF size 1	30 mm
AF size	30 mm	Protection degree	IP68 - 15 bar
Cable gland	M 25	Basic material	Brass, nickel-plated
External thread	M 25	Length of thread	7.5 mm

**Classifications**

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		