

VGM32-MS68 15-25 BG

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	Heavy-duty connectors, Accessories, Cable glands, Brass, nickel-plated
Order No.	1193610000
Type	VGM32-MS68 15-25 BG
GTIN (EAN)	403224897662 1
Qty.	25 items

VGM32-MS68 15-25 BG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Length	40 mm	Length (inches)	1.5748 inch
Net weight	99.3 g		

Temperatures

Limit temperature -40 °C ... 130 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

General information

Outer cable diameter, max.	25 mm	Outer cable diameter, min.	15 mm
O-Ring	NBR	Protection degree with GWDR	IP68
UL 94 flammability rating	V-0	Operating temperature range, max.	130 °C
Operating temperature range, min.	-40 °C	Halogen	halogen-free
Standards	EN 45545-2:2013	AF size 1	36 mm
AF size	36 mm	Protection degree	IP68 - 15 bar
Cable gland	M 32	Basic material	Brass, nickel-plated
External thread	M 32	Length of thread	8 mm

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		