


## THM VIN 101/74 GE/G

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

### General ordering data

Version	THM, Device markers, 74 x 101 mm, yellow
Order No.	<a href="#">1192750000</a>
Type	THM VIN 101/74 GE/G
GTIN (EAN)	4032248974733
Qty.	1 items

## THM VIN 101/74 GE/G

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	74 mm	Height (inches)	2.9134 inch
Width	101 mm	Width (inches)	3.9764 inch
Net weight	794 g		

### Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Adhesive	Polyacrylate adhesive	
Printing method	Thermal transfer	
Version	Self-adhesive	
Width	101 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-40 °C	
Colour	yellow	
Halogen	No	
Basic material	Vinyl film	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Approval acc. to UL 969	No	
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	
Number of markers per combination	1 Label reel = Device markers	
Operating temperature range	-40...80 °C	
Number per roll	500	

### Device markers

Halogen	No
---------	----

### Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		