

**TM 7/18 HF/HB**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration



The TM sleeves contain no halogens and virtually no pollutants. The sleeves are equipped with the TM-I 12 or TM-I 18 tags. They cover a wide range of applications for cables and lines. This system has particularly proved its worth in traffic engineering. The slim design guarantees firm seating on the conductor.

- Halogen-free
- The slim design guarantees firm seating on the conductor
- TMX 18 for mounting with cable-ties (width 3.6 mm)

**General ordering data**

Version	TM, Socket x 28 mm, Polyethylene LD, Colour: Transparent, Conductor O.D.: 20 - 30 mm
Order No.	<a href="#">1192770000</a>
Type	TM 7/18 HF/HB
GTIN (EAN)	4032248974818
Qty.	100 items

## TM 7/18 HF/HB

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	32.7 mm	Depth (inches)	1.2874 inch
Height	18 mm	Height (inches)	0.7087 inch
Width	28 mm	Width (inches)	1.1024 inch
Net weight	1.44 g		

## Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Product Carbon Footprint	Cradle to gate 0.004 kg CO2 eq.

## General data

Type of printing	neutral	Width	28 mm
UL 94 flammability rating	HB	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Colour	Transparent
Halogen	No	Basic material	Polyethylene LD
Recommended industries	Transportation, Machinery	Operating temperature range	-40...80 °C

## Conductor and cable markers

Halogen	No	Conductor cross-section, max.	240 mm <sup>2</sup>
Conductor cross-section, min.	120 mm <sup>2</sup>	Conductor O.D., max.	30 mm
Conductor O.D., min.	20 mm	Conductor O.D.	20 - 30 mm
Cross-section for connected wire	120 - 240 mm <sup>2</sup>		

## Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		