

VGM40-SS68 20-32 BG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	Heavy-duty connectors, Accessories, Cable glands, Stainless steel 1.4305 (303)
Order No.	1193590000
Type	VGM40-SS68 20-32 BG
GTIN (EAN)	4032248976614
Qty.	10 items

VGM40-SS68 20-32 BG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Length	43 mm	Length (inches)	1.6929 inch
Net weight	146.43 g		

Temperatures

Limit temperature -40 °C ... 130 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Outer cable diameter, max.	32 mm	Outer cable diameter, min.	20 mm
O-Ring	Silicone	Protection degree with GWDR	IP68
UL 94 flammability rating	V-0	Operating temperature range, max.	130 °C
Operating temperature range, min.	-40 °C	Halogen	halogen-free
Standards	EN 45545-2:2013	AF size 1	45 mm
AF size	45 mm	Protection degree	IP68 - 15 bar
Cable gland	M 40	Basic material	Stainless steel 1.4305 (303)
External thread	M 40	Length of thread	8 mm

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		