

VGM32-MS68 15-25 BG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

| | |
|------------|--|
| Version | Heavy-duty connectors, Accessories, Cable glands, Brass, nickel-plated |
| Order No. | 1193610000 |
| Type | VGM32-MS68 15-25 BG |
| GTIN (EAN) | 403224897662 1 |
| Qty. | 25 items |

VGM32-MS68 15-25 BG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Length | 40 mm | Length (inches) | 1.5748 inch |
| Net weight | 99.3 g | | |

Temperatures

Limit temperature -40 °C ... 130 °C

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | b5ff1f66-ddba-4739-9fc0-0521ddb52139 |

General information

| | | | |
|-----------------------------------|-----------------|-----------------------------------|----------------------|
| Outer cable diameter, max. | 25 mm | Outer cable diameter, min. | 15 mm |
| O-Ring | NBR | Protection degree with GWDR | IP68 |
| UL 94 flammability rating | V-0 | Operating temperature range, max. | 130 °C |
| Operating temperature range, min. | -40 °C | Halogen | halogen-free |
| Standards | EN 45545-2:2013 | AF size 1 | 36 mm |
| AF size | 36 mm | Protection degree | IP68 - 15 bar |
| Cable gland | M 32 | Basic material | Brass, nickel-plated |
| External thread | M 32 | Length of thread | 8 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000441 | ETIM 9.0 | EC000441 |
| ETIM 10.0 | EC000441 | ECLASS 14.0 | 27-14-08-01 |
| ECLASS 15.0 | 27-14-08-01 | | |