

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

### Similar to illustration

### Abbildung ähnlich

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found specifically in the process or power generation industries. The Klippon® TB MH enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB MH enclosure range has the following advantages:

- Available in 15 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Completely removable padlock tab
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Completely removable lid without a tool
- Earthing stud in the cover and base of the enclosure
- Welded mounting feet
- · International approvals

### **General ordering data**

Version	Klippon TB MH (Terminal Box - Multi Hinge), Empty enclosure, stainless steel enclosure, Height: 306 mm, Width: 306 mm, Depth: 200 mm, Gland plates: Bottom, Basic material: Stainless steel 1.4301 (304), untreated, silver
Order No.	<u>1194760003</u>
Туре	KTB MH 303020 S2N1
GTIN (EAN)	4050118107555
Qty.	1 items





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

2

2

# Technical data

Approvals			
Approvals			
ROHS	Conform		
JL File Number Search	<u>UL Website</u>		
Certificate no. (cULus)	E243298		
Dimensions and weights			
Depth	200 mm	Depth (inches)	7.874 inch
Height	306 mm	Height (inches)	12.0472 inch
Width	306 mm	Width (inches)	12.0472 inch
Mounting dimension - height	203 mm	Mounting dimension - width	332 mm
Vet weight	11736.59 g	Mounting dimension - width	332 111111
Temperatures			
- Competatures	1		
Operating temperature	-60 °C135 °C	Note: room temperature (service)	Limited to IP66 protection when used in temperatures greater that 105°C.
Environmental Product Comp	liance		
RoHS Compliance Status	Compliant with exemp	tion	
RoHS Exemption (if applicable/known)	6c		
REACH SVHC	Lead 7439-92-1		
COLD			
SCIP	8d5fcdfe-c58e-44e1-a	6b4-74d2bbccc9dd	
	8d5fcdfe-c58e-44e1-a	6b4-74d2bbccc9dd	
Cable glands, left			
Cable glands, left	2	M75	1
Cable glands, left M63 M12	2 33	M75 M50	2
Cable glands, left M63 M12 M16	2 33 22	M75 M50 M32	2 6
M63 M12 M16 M25	2 33 22 12	M75 M50	2
M63 M12 M16 M25 M40	2 33 22	M75 M50 M32	2 6
M63 M12 M16 M25 M40	2 33 22 12	M75 M50 M32	2 6
M63 M12 M16 M25 M40 Cable glands, right	2 33 22 12	M75 M50 M32	2 6
M63 M12 M16 M25 M40 Cable glands, right	2 33 22 12 5	M75 M50 M32 M20	2 6 14
M63 M12 M16 M25 M40 Cable glands, right M25 M75	2 33 22 12 5	M75 M50 M32 M20	2 6 14
Cable glands, left  M63 M12 M16 M25 M40  Cable glands, right  M25 M75 M40	2 33 22 12 5	M75 M50 M32 M20 M63 M16 M50	2 6 14 2 2 22 2
Cable glands, left  M63 M12 M16 M25 M40  Cable glands, right  M25 M75 M40 M32	2 33 22 12 5	M75 M50 M32 M20	2 6 14 2 2 22
Cable glands, left  M63 M12 M16 M25 M40  Cable glands, right  M25 M75 M40 M32 M12	2 33 22 12 5 12 1 5 6	M75 M50 M32 M20 M63 M16 M50	2 6 14 2 2 22 2
Cable glands, left  M63 M12 M16 M25 M40  Cable glands, right  M25 M75 M40 M32 M12  Cable glands, top/bottom	2 33 22 12 5 5	M75 M50 M32 M20  M63 M16 M50 M20	2 6 14 2 2 22 2 14
Cable glands, left  M63 M12 M16 M25 M40  Cable glands, right  M25 M75 M40 M32 M12  Cable glands, top/bottom	2 33 22 12 5 1 12 1 5 6 33	M75 M50 M32 M20 M63 M16 M50 M20	2 6 14 2 2 22 2 14
Cable glands, left  M63 M12 M16 M25 M40  Cable glands, right  M25 M75 M40 M32 M12  Cable glands, top/bottom  M20 M63	2 33 22 12 5 1 12 1 5 6 33	M75 M50 M32 M20  M63 M16 M50 M20  M40	2 6 14 2 2 22 2 14 40 6
Cable glands, left  M63 M12 M16 M25 M40  Cable glands, right  M25 M75 M40 M32 M12  Cable glands, top/bottom  M20 M63 M32 M32	2 33 22 12 5 1 12 1 5 6 33	M75 M50 M32 M20 M63 M16 M50 M20	2 6 14 2 2 22 2 14

Creation date 26.11.2025 10:54:46 MEZ

M50

M16

3

26

Catalogue status / Drawings

M75





# Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Certificate numbers enclosur	G		
Certificate No. UL Haz.Loc.	E223792	Declaration of Conformatiy No. (DoC LVD)	DE PS261X 160412 001ISS03
Certificate No. UL Ord.Loc.	E243298	Certificate No. UL 508A	E223801
Attestation of Conformatiy No. (AoC)	DE PS261X 160309 001ISS06	Certificate No. UL Terminal Box	E223792
Certificate No. Electronic Box (NEPSI)	2020322303003289	Certificate no. empty enclosure (ECAS)	21-09-25241/ E21-09-053807
Certificate no. empty enclosure (INMETRO)	LMP 21.0016U	Certificate No. (DNV)	TAE000013S
Certificate No. (CCOE)	P461058_1	Certificate no. Terminal Box (INMETRO)	LMP 21.0017
Certificate no. (INMETRO)	IEX17.0020U	Certificate No. (IECEX)	IECEXPTB11.0071
Certificate No. (ATEX)	PTB11ATEX2019	Approval conditions	ATEX, CCOE, DNV, IECEX, INMETRO, KC, NEPSI, CCC UL AEx Class Div., UL AEx Class Zone, cULus
Certificate no. (cULus)	E243298		
General information			
Material thickness of cover	1.5 mm	Material thickness of flange	3 mm
Material thickness of enclosure	1.5 mm	Operating temperature, max.	135 °C
Operating temperature, min.	-60 °C	Lid attachment	4 hinges and M6 hex-head slotted screws SW10
Standards	DIN EN 62208 - Empty enclosure standard, DIN EN 61373 Class 1B**, DIN EN 15085-2, EN 60079-0, EN 60079-7, EN 60079-31, IEC 60079-0, IEC 60079-7, IEC 60079-31	Surface finish	untreated
Impact resistance	7 J ATEX version, 10 J version standard	AF size	10 mm
Protection degree	IP66, IP67	Basic material	Stainless steel 1.4301 (304)
Seal material	Silicone	Torque for lid screws	2.5 Nm
Integral fixing	4, 6 or 9 stud bolts M6 inner (female) thread	Enclosure attachment	4 welded-on mounting feet with 11 mm holes (2 slotted feet and 2 cross- shaped feet)
Note: protection class	If used in temperature ranges above 105 °C, IP protection is limited to IP 66.	Flange plate mounting	M6 hexagonal head screws 10 SW
Protection class (UL)	Type 3, Type 4X, Type 12	Number of lid screws	4
Gland plates	Bottom	Dimension of box	460x500x290
Access opening: width	247 mm	Opening angle lid	130.00°
Overall dimensions	317 x 357 x 215	Flange plate	Yes
Max. payload	37 kg	Lid	Yes
Access opening: height	253 mm	Position PE bolts	Enclosure side C
Areas of use	Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore		





# Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

Housing earth			
Earth, enclosure, internal	Welded-on M6 stainless- steel earth stud in		
	enclosure body and lid.		
horizontal assembly			
WDU 10 / ZDU 10	1x20	WDU 16 / ZDU 16	1x16
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x40	WDU 35 / ZDU 35	1x12
WDU 4 / ZDU 4	2x33	WDU 6 / ZDU 6	2x25
vertical assembly			
WDU 10 / ZDU 10	1x20	WDU 16 / ZDU 16	1x17
NDU 2,5 / ZDU 2,5 / IDU 2,5	2x41	WDU 35 / ZDU 35	1x12
NDU 4 / ZDU 4	2x34	WDU 6 / ZDU 6	2x25
Important note			
Product information	Minimum order quantity (5	pieces)	
Classifications			
ETIM 6.0	EC002503	ETIM 7.0	EC002503
ETIM 8.0	EC002503 EC002503	ETIM 7.0	EC002503 EC002503
ETIM 10.0	EC002503 EC002503	ECLASS 9.0	27-18-05-02
ECLASS 9.1	27-18-05-02	ECLASS 9.0 ECLASS 10.0	27-18-05-02
ECLASS 9.1	27-18-05-02	ECLASS 10.0 ECLASS 12.0	27-16-05-02
ECLASS 11.0 ECLASS 13.0	27-18-05-02	ECLASS 12.0 ECLASS 14.0	27-18-05-02
ECLASS 15.0	27-18-05-02		27-10-03-02





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

Drawings	www.weidmueller.com
Dimensioned drawing	



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Accessories

#### 306 x 306mm

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Mounting plates

Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.

### **General ordering data**

Type	KTB MOPL 3030 MSZN	Version
Order No.	<u>1193960000</u>	Klippon TB (Terminal Box), Mounting plate, Height: 251 mm, Width:
GTIN (EAN)	4050118028560	245 mm, Depth: 1.5 mm, Basic material: Sheet steel, galvanized,
Qty.	1 ST	silver
Туре	KTB MOPL 3030 S2N	Version
Order No.	<u>1193830000</u>	Klippon TB (Terminal Box), Mounting plate, Height: 251 mm, Width:
GTIN (EAN)	4050118028430	245 mm, Depth: 1.5 mm, Basic material: Stainless steel 1.4301
Qty.	1 ST	(304), untreated, silver
•		
Туре	KTB MOPL 3030 MSZN H	Version
•	KTB MOPL 3030 MSZN H 2022190000	Version Klippon TB (Terminal Box), Mounting plate, prepunched, Height: 251
Туре		
Type Order No.	2022190000	Klippon TB (Terminal Box), Mounting plate, prepunched, Height: 251
Type Order No. GTIN (EAN)	<u>2022190000</u> 4050118403466	Klippon TB (Terminal Box), Mounting plate, prepunched, Height: 251 mm, Width: 245 mm, Depth: 1.5 mm, Basic material: Sheet steel,
Type Order No. GTIN (EAN) Qty.	2022190000 4050118403466 1 ST	Klippon TB (Terminal Box), Mounting plate, prepunched, Height: 251 mm, Width: 245 mm, Depth: 1.5 mm, Basic material: Sheet steel, galvanized, silver
Type Order No. GTIN (EAN) Oty. Type	2022190000 4050118403466 1 ST KTB MOPL 3030 S2N H	Klippon TB (Terminal Box), Mounting plate, prepunched, Height: 251 mm, Width: 245 mm, Depth: 1.5 mm, Basic material: Sheet steel, galvanized, silver  Version

### Gland plates without earthing studs

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

### **General ordering data**

Type	KTB GP XX3020V AB S4	Version
Order No.	<u>1280970000</u>	Klippon TB (Terminal Box), flange plate, straight, Height: 296 mm,
GTIN (EAN)	4050118071658	Width: 167 mm, Depth: 3 mm, Gland plates: top, Bottom, Basic
Qty.	1 ST	material: Stainless steel 1.4404 (316L), electropolished, silver

Creation date 26.11.2025 10:54:46 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Accessories**

### Gland plates made out of stainless steel - 6 mm

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

### **General ordering data**

Туре	KTB GP XX3020V AB S4 6MM	Version
Order No.	<u>1256360000</u>	Klippon TB (Terminal Box), flange plate, straight, Height: 296 mm,
GTIN (EAN)	4050118093773	Width: 167 mm, Depth: 6 mm, Gland plates: top, Bottom, Basic
Qty.	1 ST	material: Stainless steel 1.4404, electropolished, silver

#### Gland plates with earthing studs

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

### **General ordering data**

Туре	KTB GP XX3020V AB S4 PE	Version
Order No.	2023140000	Klippon TB (Terminal Box), flange plate, straight, Height: 296 mm,
GTIN (EAN)	4050118403770	Width: 167 mm, Depth: 3 mm, Gland plates: top, Bottom, Basic
Qty.	1 ST	material: Stainless steel 1.4404, Stainless steel 1.4404 (316L),
		electropolished, silver

### Stainless steel 1.4301

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Rain Covers

The rain cover provides an ideal, additional level of protection for the enclosure if it is installed in unusual climatic zones with, for instance, very heavy rainfall or extreme levels of direct sunlight.





### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Accessories

### **General ordering data**

Type	KTB RNHD 303020 R	Version
Order No.	1281400000	Klippon TB (Terminal Box), Rain hood, Height: 55.9 mm, Width: 311
GTIN (EAN)	4050118072082	mm, Depth: 221.2 mm, Basic material: Stainless steel 1.4301, Mirror
Qty.	1 ST	polished, silver

### Type label holder

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Nameplate holders

There are a variety of designed label holders available for prominent display as required and for additional nameplates as needed.

### **General ordering data**

Туре	TPSDHA KTB 100X25 S2 2R	Version
Order No.	<u>1257640000</u>	Klippon TB (Terminal Box), Ratings plate holder, Riveted, Height: 25
GTIN (EAN)	4050118070354	mm, Width: 141 mm, Depth: 16.5 mm, Basic material: Stainless steel
Qty.	1 ST	1.4301, Stainless steel 1.4301 (304), Mirror polished, silver
Туре	TPSDHA KTB 130X50 S2 R	Version
Order No.	1283450000	Klippon TB (Terminal Box), Ratings plate holder, Riveted, Height: 50
GTIN (EAN)	4050118073621	mm, Width: 171 mm, Depth: 16.5 mm, Basic material: Stainless steel
Qty.	1 ST	1.4301, Stainless steel 1.4301 (304), Mirror polished, silver
Туре	TPSDHA KTB 70X70M3 S2 R	Version
Order No.	1279320000	Klippon TB (Terminal Box), Ratings plate holder, Riveted, Height: 70
GTIN (EAN)	4050118070101	mm, Width: 70 mm, Depth: 20 mm, Basic material: Stainless steel
Qty.	1 ST	1.4301, Stainless steel 1.4301 (304), Mirror polished, silver



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Accessories**

#### Installation material

Integrate, expand and customise - the perfect supplement to every application

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

Mounting hardware kits

Mounting hardware kits are available for quick and easy installation of type label holders, document holders and rain hoods.

The label fastening set – SD is required to install a plastic (Trafolyte) ID or type label. With the aid of this set can you mount the ID or type label directly on the enclosure cover. The label fastening set has been specially developed for this purpose. Only by using this fastening set can you ensure that there will be no leaks into the enclosure or damage to the label.

The universal fastening set – TPSD has been developed to enable secure and quick installation of type label holders, rain covers or document holders, for example. By using this fastening set, the risk of leaks can be minimised, if not avoided.

### **General ordering data**

Type	SD FIXING SET	Version
Order No.	1285200000	Klippon TB (Terminal Box), Identification plate fixing set, Height: 12
GTIN (EAN)	4050118075472	mm, Width: 12 mm, Depth: 16.4 mm, Basic material: Stainless steel,
Qty.	1 ST	rust-proof, untreated, silver
Туре	TPSD FIXING SET KTB	Version
Type Order No.	TPSD FIXING SET KTB 1252190000	Version Klippon TB (Terminal Box), Type plate fixings set, Basic material:

### **Earthing stud**

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Earthing bolt

Earthing bolts to exchange as a complete component in two versions – brass and stainless steel.

#### General ordering data

Туре	PEBZ M10 KTB BR SET	Version
Order No.	1192680000	Klippon TB (Terminal Box), Earthing stud, Miscellaneous, Height:
GTIN (EAN)	4032248974641	21 mm, Width: 21 mm, Depth: 48.7 mm, Basic material: Brass,
Qty.	1 ST	untreated, silver

Creation date 26.11.2025 10:54:46 MEZ



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Accessories**

Туре	PEBZ M10 KTB S4 SET	Version
Order No.	<u>1192690000</u>	Klippon TB (Terminal Box), Earthing stud, Miscellaneous, Height: 21
GTIN (EAN)	4032248974658	mm, Width: 21 mm, Depth: 48.7 mm, Basic material: Stainless steel
Qty.	1 ST	1.4404 (316L), untreated, silver

# **Document holders**

Integrate, expand and customise - the perfect supplement to every application

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

Document holders

Document holders for the proper storage of documents in the enclosure

### **General ordering data**

Тур	e	DOHA KTB A6 S2 R	Version
Ord	ler No.	1252780000	Klippon TB (Terminal Box), Document holders, Riveted, Height: 110
GTII	N (EAN)	4050118045512	mm, Width: 130 mm, Depth: 20 mm, Basic material: Stainless steel
Qty.		1 ST	1.4301, Stainless steel 1.4301 (304), Mirror polished, silver

### **Grounding strap**

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application. The following options are available:

- Closure Elements
- Document holders
- Earthing stud
- Gland plates
- · Installation material
- Mounting plates
- Rain hoods
- Spacer
- Terminal rails
- Type label holder

# **General ordering data**

Туре	PECD WIRE 6/200/D6 SET	Version
Order No.	<u>2475490000</u>	Klippon TB (Terminal Box), Grounding strap, Ssrewed, Basic material:
GTIN (EAN)	4050118487206	Steel, Green/yellow
Qty.	1 ST	

Creation date 26.11.2025 10:54:46 MEZ



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Accessories**

### Stainless steel 1.4404 (316L)

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Rain Covers

The rain cover provides an ideal, additional level of protection for the enclosure if it is installed in unusual climatic zones with, for instance, very heavy rainfall or extreme levels of direct sunlight.

### **General ordering data**

Туре	KTB RNHD XX3020V S4E R	Version
Order No.	<u>1314130000</u>	Klippon TB (Terminal Box), Rain hood, Height: 55.9 mm, Width: 311
GTIN (EAN)	4050118117240	mm, Depth: 221.2 mm, Basic material: Stainless steel 1.4404 (316L),
Qty.	1 ST	electropolished, silver

### Depth 7.5 mm

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Terminal rails

The mounting rails are available in two sizes for mounting DIN rails (e.g. electronics, terminals) components in the enclosures.

# **General ordering data**

Type	TS35X7.5 ST KTB3030 HOR	Version
Order No.	8000006722	Rail, TS 35, TS 35 x 7.5, Width: 245 mm, without slot, Steel,
GTIN (EAN)	4050118652901	galvanized, chromium-plated
Qty.	20 ST	
Туре	TS35X7.5 ST KTB3030 VER	Version
Type Order No.	TS35X7.5 ST KTB3030 VER 8000006710	Version Rail, TS 35, TS 35 x 7.5, Width: 251 mm, without slot, Steel,

### **Mounting plates**

Mounting plates, with and without hole patterns, for longitudinal and transverse mounting of DIN mounting rails or components directly onto the mounting plate.



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# Accessories

### **General ordering data**

Туре	GFSC M5X10 TX20 SET	Version
Order No.	<u>1274150000</u>	Klippon EB (Essential Box), Mounting screw, Height: 13.3 mm, Width:
GTIN (EAN)	4050118063820	8.5 mm, Depth: 8.5 mm, Basic material: Steel, galvanized, galvanic
Qty.	1 ST	zinc plated and passivated, silver

### Depth 15 mm

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Terminal rails

The mounting rails are available in two sizes for mounting DIN rails (e.g. electronics, terminals) components in the enclosures.

### **General ordering data**

Туре	TS35X15 ST KTB3030 HOR	Version
Order No.	8000073111	Rail, TS 35, TS 35 x 15, Width: 245 mm, without slot, Steel, galvanic
GTIN (EAN)	4064675340614	zinc plated and passivated
Qty.	20 ST	
Type	TS35X15 ST KTB3030 VER	Version
Type Order No.	TS35X15 ST KTB3030 VER 8000073112	Version Rail, TS 35, TS 35 x 15, Width: 251 mm, without slot, Steel, galvanic

### **Installation material**

Integrate, expand and customise - the perfect supplement to every application

The fully structured range of system accessories for the new Klippon® TB enclosure series allows you to easily adapt the enclosures to meet the specific requirements of every application.

Mounting hardware kits

Mounting hardware kits are available for quick and easy installation of type label holders, document holders and rain hoods.

The label fastening set – SD is required to install a plastic (Trafolyte) ID or type label. With the aid of this set can you mount the ID or type label directly on the enclosure cover. The label fastening set has been specially developed for this purpose. Only by using this fastening set can you ensure that there will be no leaks into the enclosure or damage to the label.

The universal fastening set – TPSD has been developed to enable secure and quick installation of type label holders, rain covers or document holders, for example. By using this fastening set, the risk of leaks can be minimised, if not avoided.

Creation date 26.11.2025 10:54:46 MEZ





Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Accessories**

# **General ordering data**

Type FKSC M6X8 D9/SW3
Order No. 0642600000
GTIN (EAN) 4008190058258
Oty. 50 ST

Version

Klippon TB (Terminal Box), Mounting screw, Basic material: Steel