

## KTB MH 553520 S4N1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



Abbildung ähnlich

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found specifically in the process or power generation industries. The Klippon® TB MH enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB MH enclosure range has the following advantages:

- Available in 22 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Completely removable padlock tab
- Cover lock outside the sealed zone
- Improved temperature performance
- IP66/IP67 protection
- Completely removable lid – without a tool
- Earthing stud in the cover and base of the enclosure
- Welded mounting feet
- International approvals

### General ordering data

|            |                                                                                                                                                                                                                              |
|------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version    | Klippon TB MH (Terminal Box - Multi Hinge), Empty enclosure, stainless steel enclosure, Height: 550 mm, Width: 350 mm, Depth: 200 mm, Gland plates: Bottom, Basic material: Stainless steel 1.4404 (316L), untreated, silver |
| Order No.  | <a href="#">1195260002</a>                                                                                                                                                                                                   |
| Type       | KTB MH 553520 S4N1                                                                                                                                                                                                           |
| GTIN (EAN) | 4050118106060                                                                                                                                                                                                                |
| Qty.       | 1 items                                                                                                                                                                                                                      |

## KTB MH 553520 S4N1

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



|                         |                            |
|-------------------------|----------------------------|
| ROHS                    | Conform                    |
| UL File Number Search   | <a href="#">UL Website</a> |
| Certificate no. (cULus) | E243298                    |

### Dimensions and weights

|                             |            |                            |              |
|-----------------------------|------------|----------------------------|--------------|
| Depth                       | 200 mm     | Depth (inches)             | 7.874 inch   |
| Height                      | 550 mm     | Height (inches)            | 21.6535 inch |
| Width                       | 350 mm     | Width (inches)             | 13.7795 inch |
| Mounting dimension - height | 350 mm     | Mounting dimension - width | 376 mm       |
| Net weight                  | 16573.43 g |                            |              |

### Temperatures

|                       |                 |                                  |                                                                           |
|-----------------------|-----------------|----------------------------------|---------------------------------------------------------------------------|
| Operating temperature | -60 °C...135 °C | Note: room temperature (service) | Limited to IP66 protection when used in temperatures greater than 105 °C. |
|-----------------------|-----------------|----------------------------------|---------------------------------------------------------------------------|

### Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 8d5fcdfe-c58e-44e1-a6b4-74d2bbccc9dd |

### Cable glands, left

|     |    |     |    |
|-----|----|-----|----|
| M63 | 4  | M75 | 3  |
| M12 | 70 | M50 | 5  |
| M16 | 48 | M32 | 14 |
| M25 | 26 | M20 | 30 |
| M40 | 12 |     |    |

### Cable glands, right

|     |    |     |    |
|-----|----|-----|----|
| M25 | 26 | M63 | 4  |
| M75 | 3  | M16 | 48 |
| M40 | 12 | M50 | 5  |
| M32 | 14 | M20 | 30 |
| M12 | 70 |     |    |

**KTB MH 553520 S4N1**
**Weidmüller Interface GmbH & Co. KG**

 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data**
**Cable glands, top/bottom**

|     |    |     |    |
|-----|----|-----|----|
| M20 | 20 | M12 | 45 |
| M63 | 3  | M40 | 7  |
| M32 | 9  | M25 | 17 |
| M50 | 3  | M75 | 2  |
| M16 | 30 |     |    |

**Certificate numbers enclosure**

|                                           |                           |                                         |                                                                                              |
|-------------------------------------------|---------------------------|-----------------------------------------|----------------------------------------------------------------------------------------------|
| Certificate No. UL Haz.Loc.               | E223792                   | Declaration of Conformity No. (DoC LVD) | DE PS261X 160412 001ISS03                                                                    |
| Certificate No. UL Ord.Loc.               | E243298                   | Certificate No. UL 508A                 | E223801                                                                                      |
| Attestation of Conformity No. (AoC)       | DE PS261X 160309 001ISS06 | Certificate No. UL Terminal Box         | E223792                                                                                      |
| Certificate No. Electronic Box (NEPSI)    | 2020322303003289          | Certificate no. empty enclosure (ECAS)  | 21-09-25241/<br>E21-09-053807                                                                |
| Certificate no. empty enclosure (INMETRO) | LMP 21.0016U              | Certificate No. (DNV)                   | TAE000013S                                                                                   |
| Certificate No. (CCOE)                    | P461058_1                 | Certificate no. Terminal Box (INMETRO)  | LMP 21.0017                                                                                  |
| Certificate no. (INMETRO)                 | IEX13.0006U               | Certificate No. (IECEX)                 | IECEXPTB11.0071                                                                              |
| Certificate No. (ATEX)                    | PTB11ATEX2019             | Approval conditions                     | ATEX, CCoE, DNV, IECEX, INMETRO, KC, NEPSI, CCC, UL AEx Class Div., UL AEx Class Zone, cULus |
| Certificate no. (cULus)                   | E243298                   |                                         |                                                                                              |

**General information**

|                                 |                                                                                                                                                               |                              |                                                                                     |
|---------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------|-------------------------------------------------------------------------------------|
| Material thickness of cover     | 1.5 mm                                                                                                                                                        | Material thickness of flange | 3 mm                                                                                |
| Material thickness of enclosure | 1.5 mm                                                                                                                                                        | Operating temperature, max.  | 135 °C                                                                              |
| Operating temperature, min.     | -60 °C                                                                                                                                                        | Lid attachment               | 4 hinges and M6 hex-head slotted screws SW10                                        |
| Standards                       | DIN EN 62208 - Empty enclosure standard, DIN EN 61373 Class 1B**, DIN EN 15085-2, EN 60079-0, EN 60079-7, EN 60079-31, IEC 60079-0, IEC 60079-7, IEC 60079-31 | Surface finish               | untreated                                                                           |
| Impact resistance               | 7 J ATEX version, 10 J version standard                                                                                                                       | AF size                      | 10 mm                                                                               |
| Protection degree               | IP66, IP67                                                                                                                                                    | Basic material               | Stainless steel 1.4404 (316L)                                                       |
| Seal material                   | Silicone                                                                                                                                                      | Torque for lid screws        | 2.5 Nm                                                                              |
| Integral fixing                 | 4, 6 or 9 stud bolts M6 inner (female) thread                                                                                                                 | Enclosure attachment         | 4 welded-on mounting feet with 11 mm holes (2 slotted feet and 2 cross-shaped feet) |
| Note: protection class          | If used in temperature ranges above 105 °C, IP protection is limited to IP 66.                                                                                | Flange plate mounting        | M6 hexagonal head screws 10 SW                                                      |
| Protection class (UL)           | Type 3, Type 4X, Type 12                                                                                                                                      | Number of lid screws         | 8                                                                                   |
| Gland plates                    | Bottom                                                                                                                                                        | Dimension of box             | 550x710x290                                                                         |
| Access opening: width           | 291 mm                                                                                                                                                        | Opening angle lid            | 130.00 °                                                                            |
| Overall dimensions              | 561 x 401 x 215                                                                                                                                               | Flange plate                 | Yes                                                                                 |
| Max. payload                    | 77 kg                                                                                                                                                         | Lid                          | Yes                                                                                 |

**KTB MH 553520 S4N1**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

|                        |                                                                                                      |                   |                  |
|------------------------|------------------------------------------------------------------------------------------------------|-------------------|------------------|
| Access opening: height | 497 mm                                                                                               | Position PE bolts | Enclosure side C |
| Areas of use           | Explosive risk zone,<br>Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore |                   |                  |

**Housing earth**

|                            |                                                                    |  |  |
|----------------------------|--------------------------------------------------------------------|--|--|
| Earth, enclosure, internal | Welded-on M6 stainless-steel earth stud in enclosure body and lid. |  |  |
|----------------------------|--------------------------------------------------------------------|--|--|

**horizontal assembly**

|                             |      |                 |      |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10             | 3x24 | WDU 16 / ZDU 16 | 3x20 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 4x48 | WDU 35 / ZDU 35 | 2x15 |
| WDU 4 / ZDU 4               | 4x40 | WDU 6 / ZDU 6   | 4x30 |

**vertical assembly**

|                             |      |                 |      |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10             | 2x45 | WDU 16 / ZDU 16 | 1x37 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 2x89 | WDU 35 / ZDU 35 | 1x28 |
| WDU 4 / ZDU 4               | 2x73 | WDU 6 / ZDU 6   | 2x55 |

**Important note**

|                     |                                   |  |  |
|---------------------|-----------------------------------|--|--|
| Product information | Minimum order quantity (5 pieces) |  |  |
|---------------------|-----------------------------------|--|--|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002503    | ETIM 9.0    | EC002503    |
| ETIM 10.0   | EC002503    | ECLASS 14.0 | 27-18-05-02 |
| ECLASS 15.0 | 27-18-05-02 |             |             |

