

KTB QL 352620 S4E2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Abbildung ähnlich

The Klippon® TB enclosure range provides excellent performance characteristics, even under the most difficult environmental conditions. In addition, it complies with the stricter requirements of potentially explosive atmospheres found specifically in the process or power generation industries. The Klippon® TB QL enclosure range offers further improvements to a product line that is already successfully leading the market.

The Klippon® TB QL enclosure series features the following advantages:

- Available in 19 sizes and 3 standard depths
- Equipped with up to 4 gland plates
- The gasket is protected against compression
- Quick-locking cover, comes with a slot as standard
- Improved temperature performance
- IP66 protection
- Earthing stud in the cover and base of the enclosure
- Welded mounting feet
- International approvals

General ordering data

| | |
|------------|--|
| Version | Klippon TB QL (Terminal Box - Quarter Lock), Empty enclosure, stainless steel enclosure, Height: 350 mm, Width: 260 mm, Depth: 200 mm, Gland plates: Bottom, top, Basic material: Stainless steel 1.4404 (316L), electropolished, silver |
| Order No. | 1200180000 |
| Type | KTB QL 352620 S4E2 |
| GTIN (EAN) | 4032248982936 |
| Qty. | 1 items |

KTB QL 352620 S4E2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E243298 |

Dimensions and weights

| | | | |
|-----------------------------|--------|----------------------------|--------------|
| Depth | 200 mm | Depth (inches) | 7.874 inch |
| Height | 350 mm | Height (inches) | 13.7795 inch |
| Width | 260 mm | Width (inches) | 10.2362 inch |
| Mounting dimension - height | 250 mm | Mounting dimension - width | 286 mm |
| Net weight | 8950 g | | |

Temperatures

| | | | |
|-----------------------|-----------------|----------------------------------|---|
| Operating temperature | -60 °C...135 °C | Note: room temperature (service) | Limited to IP66 protection when used in temperatures greater than 105 °C. |
|-----------------------|-----------------|----------------------------------|---|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 8d5fcdfe-c58e-44e1-a6b4-74d2bbccc9dd |

Cable glands, left

| | | | |
|-----|----|-----|----|
| M63 | 2 | M75 | 2 |
| M12 | 38 | M50 | 3 |
| M16 | 26 | M32 | 7 |
| M25 | 14 | M20 | 17 |
| M40 | 6 | | |

Cable glands, right

| | | | |
|-----|----|-----|----|
| M25 | 14 | M63 | 2 |
| M75 | 2 | M16 | 26 |
| M40 | 6 | M50 | 3 |
| M32 | 7 | M20 | 17 |
| M12 | 38 | | |

Cable glands, top/bottom

| | | | |
|-----|----|-----|----|
| M20 | 14 | M12 | 33 |
| M63 | 2 | M40 | 5 |

KTB QL 352620 S4E2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | | |
|-----|----|-----|----|
| M32 | 6 | M25 | 12 |
| M50 | 2 | M75 | 1 |
| M16 | 22 | | |

Certificate numbers enclosure

| | | | |
|---|---------------------------|---|--|
| Certificate No. UL Haz.Loc. | E223792 | Declaration of Conformatiy No. (DoC LVD) | DE PS261X 160412 001ISS03 |
| Certificate No. UL Ord.Loc. | E243298 | Certificate No. UL 508A | E223801 |
| Attestation of Conformatiy No. (AoC) | DE PS261X 160309 001ISS06 | Certificate No. UL Terminal Box | E223792 |
| Certificate No. Electronic Box (NEPSI) | 2020322303003289 | Certificate no. empty enclosure (ECAS) | 21-09-25241/ E21-09-053807 |
| Certificate no. Terminal Box (KOSHA) | 16-AV4BO-0245X | Certificate no. empty enclosure (INMETRO) | LMP 21.0016U |
| Certificate No. (DNV) | TAE000013S | Certificate no. Terminal Box (AEx) | E223792 |
| Certificate No. (CCOE) | P461058_1 | Certificate no. Terminal Box (ATEX) | IBExU14ATEX1050 |
| Certificate no. empty enclosure (ATEX) | IBExU14ATEX1028 U | Certificate no. Terminal Box (INMETRO) | LMP 21.0017 |
| Certificate no. (INMETRO) | IEX13.0009 | Certificate no. Terminal Box (IECEX) | IECEXIBE14.0013 |
| Certificate no. empty enclosure (IECEX) | IECEX IBE 14.0004U | Certificate No. (IECEX) | IECEXKEM10.0015U |
| Certificate No. (ATEX) | KEMA10ATEX0051 | Approval conditions | ATEX, CCoE, DNV, IECEX, INMETRO, KC, NEPSI, CCC, UL AEx Class Div., UL AEx Class Zone, cULus |
| Certificate no. (cULus) | E243298 | | |

General information

| | | | |
|---------------------------------|---|------------------------------|---|
| Material thickness of cover | 1.5 mm | Material thickness of flange | 3 mm |
| Material thickness of enclosure | 1.5 mm | Operating temperature, max. | 135 °C |
| Operating temperature, min. | -60 °C | Lid attachment | Quarter-turn fastener with slotted insert |
| Standards | DIN EN 62208 - Empty enclosure standard, DIN EN 61373 Class 1B**, DIN EN 15085-2, EN 60079-0, EN 60079-7, EN 60079-31, IEC 60079-0, IEC 60079-7, IEC 60079-31 | Surface finish | electropolished |
| Impact resistance | 7 J ATEX version, 10 J version standard | AF size | 10 mm |
| Protection degree | IP66 | Basic material | Stainless steel 1.4404 (316L) |
| Seal material | Silicone | Integral fixing | 4, 6 or 9 stud bolts M6 inner (female) thread |
| Enclosure attachment | 4 welded-on mounting feet with 11 mm holes (2 slotted feet and 2 cross-shaped feet) | Note: protection class | If used in temperature ranges above 105 °C, IP protection is limited to IP 66. |
| Flange plate mounting | M6 hexagonal head screws 10 SW | Protection class (UL) | Type 3, Type 4X, Type 12 |
| Gland plates | Bottom, top | Dimension of box | 450x510x290 |
| Access opening: width | 201 mm | Opening angle lid | 130.00 ° |
| Overall dimensions | 372 x 311 x 210 | Flange plate | Yes |
| Max. payload | 36 kg | Access opening: height | 297 mm |
| Position PE bolts | Enclosure side C | Areas of use | Explosive risk zone, Process industry, Oil and gas industry, Chemical industry, Offshore, Onshore |

Technical data

Housing earth

Earth, enclosure, internal Welded-on M6 stainless-steel earth stud in enclosure body and lid.

horizontal assembly

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 2x17 | WDU 16 / ZDU 16 | 1x14 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 2x34 | WDU 35 / ZDU 35 | 1x11 |
| WDU 4 / ZDU 4 | 2x29 | WDU 6 / ZDU 6 | 2x22 |

vertical assembly

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 1x27 | WDU 16 / ZDU 16 | 1x22 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 2x53 | WDU 4 / ZDU 4 | 1x44 |
| WDU 6 / ZDU 6 | 1x33 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002503 | ETIM 9.0 | EC002503 |
| ETIM 10.0 | EC002503 | ECLASS 14.0 | 27-18-05-02 |
| ECLASS 15.0 | 27-18-05-02 | | |

KTB QL 352620 S4E2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

