


**ZVLD 2.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Product image**

To feed through power, signal, and data is the classical requirement in electrical engineering and panel building. The insulating material, the connection system and the design of the terminal blocks are the differentiating features. A feed-through terminal block is suitable for joining and/or connecting one or more conductors. They could have one or more connection levels that are on the same potential or insulated against one another.

**General ordering data**

Version	Multi-tier modular terminal, Tension-clamp connection, 2.5 mm <sup>2</sup> , 250 V, 20 A, dark beige
Order No.	<a href="#">1208920000</a>
Type	ZVLD 2.5
GTIN (EAN)	4032248990320
Qty.	50 items

## ZVLD 2.5

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	85 mm	Depth (inches)	3.3464 inch
Depth including DIN rail	86 mm	Height	148 mm
Height (inches)	5.8268 inch	Width	5.1 mm
Width (inches)	0.2008 inch	Net weight	27 g

## Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

## System specifications

Version	Tension-clamp connection, for plug-in cross-connector, One end without connector	End cover plate required	Yes
Number of potentials	4	Number of levels	4
Number of clamping points per level	2	Levels cross-connected internally	No
PE connection	No	Mounting rail	TS 35

## Additional technical data

Installation advice	Direct mounting	Explosion-tested version	No
Type of mounting	Snap-on		

## Conductors for clamping (additional connection)

Connection type, additional connection Screw connection

## Conductors for clamping (rated connection)

Gauge to IEC 60947-1	A2
Wire connection cross section AWG, max.	AWG 16
Connection direction	top
Stripping length	10 mm
Type of connection 2	Screw connection
Type of connection	Tension-clamp connection
Number of connections	8
Clamping range, max.	2.5 mm <sup>2</sup>
Clamping range, min.	0.14 mm <sup>2</sup>

## ZVLD 2.5

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Blade size	0.6 x 3.5 mm																																																																								
Wire connection cross section AWG, min.	AWG 26																																																																								
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	2.5 mm <sup>2</sup>																																																																								
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.14 mm <sup>2</sup>																																																																								
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	2.5 mm <sup>2</sup>																																																																								
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.14 mm <sup>2</sup>																																																																								
Wire connection cross section, finely stranded, max.	2.5 mm <sup>2</sup>																																																																								
Wire connection cross section, finely stranded, min.	0.14 mm <sup>2</sup>																																																																								
Connection cross-section, stranded, max.	2.5 mm <sup>2</sup>																																																																								
Connection cross-section, stranded, min. 0.14 mm <sup>2</sup>																																																																									
Wire connection cross-section, solid core, max.	2.5 mm <sup>2</sup>																																																																								
Wire connection cross-section, solid core, min.	0.14 mm <sup>2</sup>																																																																								
Connection cross-section, finely stranded, min.	0.14 mm <sup>2</sup>																																																																								
Tube length for wire-end ferrule with plastic collar DIN 46228/4	<table border="1"> <tr> <td>Tube length</td> <td>min.</td> <td>6 mm</td> </tr> <tr> <td></td> <td>max.</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.5 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>min.</td> <td>6 mm</td> </tr> <tr> <td></td> <td>max.</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.75 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>min.</td> <td>6 mm</td> </tr> <tr> <td></td> <td>max.</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>min.</td> <td>8 mm</td> </tr> <tr> <td></td> <td>max.</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1.5 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>nominal</td> <td>8 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>2.5 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>nominal</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.5 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>nominal</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.75 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>nominal</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>nominal</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1.5 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>nominal</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>2.5 mm<sup>2</sup></td> </tr> </table>	Tube length	min.	6 mm		max.	10 mm	Cross-section for conductor connection	nominal	0.5 mm <sup>2</sup>	Tube length	min.	6 mm		max.	10 mm	Cross-section for conductor connection	nominal	0.75 mm <sup>2</sup>	Tube length	min.	6 mm		max.	10 mm	Cross-section for conductor connection	nominal	1 mm <sup>2</sup>	Tube length	min.	8 mm		max.	10 mm	Cross-section for conductor connection	nominal	1.5 mm <sup>2</sup>	Tube length	nominal	8 mm	Cross-section for conductor connection	nominal	2.5 mm <sup>2</sup>	Tube length	nominal	10 mm	Cross-section for conductor connection	nominal	0.5 mm <sup>2</sup>	Tube length	nominal	10 mm	Cross-section for conductor connection	nominal	0.75 mm <sup>2</sup>	Tube length	nominal	10 mm	Cross-section for conductor connection	nominal	1 mm <sup>2</sup>	Tube length	nominal	10 mm	Cross-section for conductor connection	nominal	1.5 mm <sup>2</sup>	Tube length	nominal	10 mm	Cross-section for conductor connection	nominal	2.5 mm <sup>2</sup>
Tube length	min.	6 mm																																																																							
	max.	10 mm																																																																							
Cross-section for conductor connection	nominal	0.5 mm <sup>2</sup>																																																																							
Tube length	min.	6 mm																																																																							
	max.	10 mm																																																																							
Cross-section for conductor connection	nominal	0.75 mm <sup>2</sup>																																																																							
Tube length	min.	6 mm																																																																							
	max.	10 mm																																																																							
Cross-section for conductor connection	nominal	1 mm <sup>2</sup>																																																																							
Tube length	min.	8 mm																																																																							
	max.	10 mm																																																																							
Cross-section for conductor connection	nominal	1.5 mm <sup>2</sup>																																																																							
Tube length	nominal	8 mm																																																																							
Cross-section for conductor connection	nominal	2.5 mm <sup>2</sup>																																																																							
Tube length	nominal	10 mm																																																																							
Cross-section for conductor connection	nominal	0.5 mm <sup>2</sup>																																																																							
Tube length	nominal	10 mm																																																																							
Cross-section for conductor connection	nominal	0.75 mm <sup>2</sup>																																																																							
Tube length	nominal	10 mm																																																																							
Cross-section for conductor connection	nominal	1 mm <sup>2</sup>																																																																							
Tube length	nominal	10 mm																																																																							
Cross-section for conductor connection	nominal	1.5 mm <sup>2</sup>																																																																							
Tube length	nominal	10 mm																																																																							
Cross-section for conductor connection	nominal	2.5 mm <sup>2</sup>																																																																							
Tube length for wire-end ferrule without plastic collar DIN 46228/1	<table border="1"> <tr> <td>Tube length</td> <td>nominal</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.5 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>nominal</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>0.75 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>nominal</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>nominal</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>1.5 mm<sup>2</sup></td> </tr> <tr> <td>Tube length</td> <td>nominal</td> <td>10 mm</td> </tr> <tr> <td>Cross-section for conductor connection</td> <td>nominal</td> <td>2.5 mm<sup>2</sup></td> </tr> </table>	Tube length	nominal	10 mm	Cross-section for conductor connection	nominal	0.5 mm <sup>2</sup>	Tube length	nominal	10 mm	Cross-section for conductor connection	nominal	0.75 mm <sup>2</sup>	Tube length	nominal	10 mm	Cross-section for conductor connection	nominal	1 mm <sup>2</sup>	Tube length	nominal	10 mm	Cross-section for conductor connection	nominal	1.5 mm <sup>2</sup>	Tube length	nominal	10 mm	Cross-section for conductor connection	nominal	2.5 mm <sup>2</sup>																																										
Tube length	nominal	10 mm																																																																							
Cross-section for conductor connection	nominal	0.5 mm <sup>2</sup>																																																																							
Tube length	nominal	10 mm																																																																							
Cross-section for conductor connection	nominal	0.75 mm <sup>2</sup>																																																																							
Tube length	nominal	10 mm																																																																							
Cross-section for conductor connection	nominal	1 mm <sup>2</sup>																																																																							
Tube length	nominal	10 mm																																																																							
Cross-section for conductor connection	nominal	1.5 mm <sup>2</sup>																																																																							
Tube length	nominal	10 mm																																																																							
Cross-section for conductor connection	nominal	2.5 mm <sup>2</sup>																																																																							

## General

Wire connection cross section AWG, max.	AWG 16	Installation advice	Direct mounting
Wire connection cross section AWG, min.	AWG 26	Standards	IEC 60947-7-1
Mounting rail	TS 35		

**ZVLD 2.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Rating data**

Rated cross-section	2.5 mm <sup>2</sup>	Rated voltage	250 V
Rated DC voltage	250 V	Nominal current	20 A
Current at maximum wires	20 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	1.33 mΩ	Rated impulse withstand voltage	6 kV
Power loss in accordance with IEC 60947-7-x	0.77 W	Pollution severity	3

**Classifications**

ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 14.0	27-25-01-02
ECLASS 15.0	27-25-01-02		

**Drawings**

## ZVLD 2.5

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

Type	ZQV 2.5/2	Version
Order No.	<a href="#">1608860000</a>	Z-series, Cross-connector, 24 A
GTIN (EAN)	4008190123680	
Qty.	60 ST	
Type	ZQV 2.5/3	Version
Order No.	<a href="#">1608870000</a>	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190061630	
Qty.	60 ST	
Type	ZQV 2.5/4	Version
Order No.	<a href="#">1608880000</a>	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190082208	
Qty.	60 ST	
Type	ZQV 2.5/10	Version
Order No.	<a href="#">1608940000</a>	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190099060	
Qty.	20 ST	
Type	ZQV 2.5/20	Version
Order No.	<a href="#">1908960000</a>	Z-series, Cross-connector, For the terminals, Number of poles: 20
GTIN (EAN)	4032248535293	
Qty.	20 ST	

## End plates and partition plates



Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

## General ordering data

Type	ZAP ZVLD 2.5	Version
Order No.	<a href="#">1210410000</a>	Z-series, End plate
GTIN (EAN)	4032248991440	
Qty.	10 ST	

## ZVLD 2.5

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

Type	ZEW 35/2	Version
Order No.	<a href="#">8630740000</a>	End bracket, dark beige, TS 35, V-2, Wemid, Width: 8 mm, 100 °C
GTIN (EAN)	4032248348916	
Qty.	20 ST	

## Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

## General ordering data

Type	ZTA ZVLD	Version
Order No.	<a href="#">1210390000</a>	Accessories, Test adapter, 6 A
GTIN (EAN)	4032248991426	
Qty.	50 ST	
Type	ZTA ZVLD/ZA	Version
Order No.	<a href="#">1271870000</a>	Accessories, Test adapter, 6 A
GTIN (EAN)	4050118060850	
Qty.	50 ST	

## ZVLD 2.5

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.


- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/5 MC NE WS	Version
Order No.	<a href="#">1609801044</a>	Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00
GTIN (EAN)	4008190397111	Weidmüller, white
Qty.	1000 ST	

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

Type	ZVQ 2.5/1.5	Version
Order No.	<a href="#">1720700000</a>	Accessories, Cross-connector, 24 A
GTIN (EAN)	4008190374006	
Qty.	50 ST	

## Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

**ZVLD 2.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****General ordering data**

Type	SDIS SLIM 0.6X3.5X100	Version
Order No.	<a href="#">2749610000</a>	Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade
GTIN (EAN)	4050118896350	thickness (A): 0.6 mm
Qty.	1 ST	