

SAIL-M8GRJ45-4S20UIE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The most reliable way of achieving connections between two I/O slaves or between the control and one I/O subscriber is by way of pre-assembled cables. The line of cables covers PROFIBUS, CANopen, DeviceNet™, Ether-CAT and Ethernet.

General ordering data

Version	Bus line, Number of poles: 4, 20 m, pin, straight, RJ45, Shielded: Yes, LED: No, Sheath material: PUR, Halogen: No
Order No.	1201212000
Type	SAIL-M8GRJ45-4S20UIE
GTIN (EAN)	4050118692747
Qty.	1 items

SAIL-M8GRJ45-4S20UIE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS Conform

Dimensions and weights

Net weight 529.76 g

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption
 RoHS Exemption (if applicable/known) 6c
 REACH SVHC Lead 7439-92-1
 SCIP e8d8af70-4c85-4483-bc8c-9bc5b598e2a9

Technical specifications for cable

Cable length	20 m	Sheathing colour	green
Resistance to oils	Yes	Suitable for cable carriers	Yes
Core cross-section	0.15 mm ²	Shielded	Yes
Halogen	No	Insulation	PP
Acceleration	5 m/s ²	Bending radius, min., moving	7.5 x cable diameter
Bending radius, min., stationary	4 x cable diameter	Bending cycles	5 Mio
Resistance to spread of flame	in accordance with IEC 60332-1-2	Speed	180 m/s
Sheath material	PUR	Outer cladding in accordance with UL AWM style	20963 (80 °C / 30 V)
Hybrid cable	No	Colour coding	blue, orange, white / blue, white / orange
Temperature range, stationary	-40...80 °C	Number of poles	4
Outside diameter	4.8 mm ± 0.3 mm		

General technical data

Coding	none	Contact surface	Gold-plated
LED	No	Version	pin, straight, RJ45
Housing main material	PUR	Nominal voltage	30 V
Nominal current	4 A	Protection degree	IP67
Pollution severity	3	jumpered	No
Threaded ring material	Brass, nickel-plated	Temperature range of housing	-25...+80 °C
Tightening torque	M8: 0.6 Nm		

Electrical properties

Nominal voltage 30 V

Plug, left

Plug left connector, M8, Number of poles: 4, IP67, male contact, straight, shielded

SAIL-M8GRJ45-4S20UIE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Plug, right**

Plug right	connector, RJ45, IP20, male contact, straight, shielded
------------	---

Classifications

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		


SAIL-M8GRJ45-4S20UIE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com


Drawings

Dimensioned drawing



Male, straight

Dimensioned drawing




RJ45

Pole scheme



Pin

Pole scheme



RJ45

Drawings

Wiring diagram



The ideal tool: Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F