

**A2LC/20S/NPT1/2-NPT3/4F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

A2LC type cable glands are suitable for un-armored cable and provide a conduit connection female thread, maintains flameproof Ex d and Increased Safety Ex e explosion protection.

**General ordering data**

Version	A2LC (Klippon unarmored with conduit connection thread, Ex e/d cable gland), Cable glands, straight, 1/2" NPT, 13.6 mm, OD min. 8 - OD max. 11.7 mm, Brass, nickel-plated
Order No.	<a href="#">1205960000</a>
Type	A2LC/20S/NPT1/2-NPT3/4F
GTIN (EAN)	4050118078268
Qty.	24 items
Delivery status	Discontinued
Available until	2024-08-31T00:00:00+02:00

## A2LC/20S/NPT1/2-NPT3/4F

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Height	52.8 mm	Height (inches)	2.0787 inch
Width	28.5 mm	Width (inches)	1.122 inch
Length	68.8 mm	Length (inches)	2.7087 inch
Net weight	140 g		

## Temperatures

Operating temperature -50 °C... 120 °C

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	9706e29a-947e-49f2-a4db-8015ded62160

## Certificate numbers cable gland

Identification	II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da	Certificate no. cable gland (ATEX)	TÜV IT 16ATEX 059X
Certificate no. cable gland (IECEX)	IECEX TPS 16.0004X	Certificate no. cable gland (CCC)	2020322313000069
Certificate No. (IECEX)	IECEXTPS16.0004X		

## General information

Outer cable diameter, max.	11.7 mm	Outer cable diameter, min.	8 mm
O-Ring	Silicone	Tightening torque	20 Nm
Silicone	Yes	Operating temperature range, max.	120 °C
Operating temperature range, min.	-50 °C	Pitch of thread	1.81 mm
Halogen	No	Standards	EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7
AF size 1	26 mm	AF size 2	26 mm
Protection degree	IP66, IP68	Cable gland	NPT 1/2"
Basic material	Brass, nickel-plated	Seal insert	Silicone
Sealing	Silicone	External thread	1/2" NPT
Length of thread	13.6 mm	Explosion protection type	Ex d - flameproof, Ex e - increased safety
Installation guidelines	See assembly instructions	Conduit thread size (Inch)	NPT 3/4"

## A2LC/20S/NPT1/2-NPT3/4F

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-04
ECLASS 15.0	27-14-08-04		