

**HDC 32B TSBU 1M40G CS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

Version	HDC enclosures, Installation size: 10, Protection degree: IP65, in plugged condition, Cable entry from side, Side-locking clamp on lower side, Standard, Size of cable entries: M 40
Order No.	<a href="#">1221060000</a>
Type	HDC 32B TSBU 1M40G CS
GTIN (EAN)	4032248998173
Qty.	1 items

## HDC 32B TSB 1M40G CS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Depth	94 mm	Depth (inches)	3.7008 inch
Height	79 mm	Height (inches)	3.1102 inch
Width	98 mm	Width (inches)	3.8583 inch
Net weight	334.4 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Dimensions

Cable entry	w. thread	Width housing C	82.5 mm
Total length housing	94 mm	Height of housing B	79 mm

## General data

Tightening torque	2 Nm	Housing main material	diecast aluminium
Surface finish	Powder coating	Protection degree	IP65, in plugged condition
EMC housings	No	Material of locking element	Stainless steel, rust-proof

## Version

Size of cable entries	M 40	Top part/bottom part/lid	upper part
Tightening torque	2 Nm	Number of cable entry on top	0
Number of cable entry sideways	1	Design of housing	Cable entry from side
Design of locking system	Side-locking clamp on lower side	Design	Standard
Installation size	10	Cable entry	w. thread
Type	Plug	Colour (RAL)	RAL 5015
BG	10	Suitable for ModuPlug®	Yes

## Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02
ECLASS 13.0	27-44-02-02	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		