

THM VIN 36/18 SI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

Version	THM, Device markers, 18 x 36 mm, silver
Order No.	1209010000
Type	THM VIN 36/18 SI
GTIN (EAN)	4032248990108
Qty.	1 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	18 mm	Height (inches)	0.7087 inch
Width	36 mm	Width (inches)	1.4173 inch
Net weight	300 g		

Temperatures

Operating temperature range	-50...90 °C
-----------------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Adhesive	Polyacrylate adhesive	
Printing method	Thermal transfer	
Version	Self-adhesive	
Width	36 mm	
UL 94 flammability rating	V-0	
Operating temperature range, max.	90 °C	
Operating temperature range, min.	-50 °C	
Colour	silver	
Halogen	Yes	
Basic material	Vinyl film	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Approval acc. to UL 969 compatible printer	No	
Number of markers per combination	1 Label reel = Device markers	
Operating temperature range	-50...90 °C	
Number per roll	2500	

Device markers

Halogen	Yes
---------	-----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		