

FTA-C300-16AO-SH-Z


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

Analogue input/output direct FTAs for Honeywell C300 IOTAs.

Passive interfaces (FTA) for connecting the Honeywell C300 analog IOTAs.

- Clearly labelled: Same connector and position on the FTA and on the IOTA.
- 2 units may also be used for the digital IOTAs.
- Disconnecting plugs and test points (2mm in diameter) for voltage and current measurements.
- The FTAs incorporate an M4 connection for the shielding.
- Screw or tension clamp connection

General ordering data

Version	Interface, RS, 1-wire, Tension-clamp connection
Order No.	1222990000
Type	FTA-C300-16AO-SH-Z
GTIN (EAN)	4050118006278
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2026-02-10T00:00:00+01:00

FTA-C300-16AO-SH-Z

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E141197

Dimensions and weights

Depth	56 mm	Depth (inches)	2.2047 inch
Height	70 mm	Height (inches)	2.7559 inch
Width	105 mm	Width (inches)	4.1338 inch
Net weight	153.12 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	2e4a427f-c282-4ebf-8ee2-8af7c9348f4e

Rated data UL

Rated current IN	1 A	Operating temperature UL, min.	-25 °C
Operating temperature UL, max.	50 °C	Rated voltage UN	250V AC / 350 V DC

General data

LED status display per channel	No	Disconnection per channel	No
Voltage point of measurement	No	Current-measuring testpoint	No
Type of test point	No	Contactors	No
Fuse per channel	No	LED status of the supply voltage	No
Power supply fuse	No		

Connection data

Number of poles (control side)	32-pole female	Protective earth connection	M4 round terminal
Wiring system	1-wire	Connection (field side)	LM2NZF 5.08mm
Connection on control side	SLDV-THR 5.08		

Ratings data

Operating voltage	250 V AC / 350 V DC	Max. current per channel	1 A
-------------------	---------------------	--------------------------	-----

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	<250 V AC
Surge voltage category	II	Pollution severity level	2
Pulse voltage test (1,2/50µs)	2 kV	Insulation test voltage AC	1.2 kV

FTA-C300-16AO-SH-Z

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Connection field

Min. wire cross-section, AWG	AWG 24	Type of connection	Tension-clamp connection
Sleeve with plastic collar, max.	1.5 mm ²	Flexible with sleeve, min.	0.25 mm ²
Flexible with sleeve, max.	1.5 mm ²	Flexible, max. H05(07) V-K	1.5 mm ²
Flexible, min. H05(07) V-K	0.2 mm ²	Solid, max. H05(07) V-U	2.5 mm ²
Solid, min. H05(07) V-U	0.2 mm ²	Stripping length	7.5 mm
Clamping range, max.	2.5 mm ²	Clamping range, min.	0.13 mm ²
Max. wire cross-section, AWG	AWG 14		

Supply connection

Type of connection	Tension-clamp connection	Clamping range, min.	0.13 mm ²
Clamping range, max.	2.5 mm ²	Solid, min. H05(07) V-U	0.2 mm ²
Solid, max. H05(07) V-U	2.5 mm ²	Flexible, min. H05(07) V-K	0.2 mm ²
Flexible, max. H05(07) V-K	1.5 mm ²	Flexible with sleeve, max.	1.5 mm ²
Flexible with sleeve, min.	0.25 mm ²	Ferrule with plastic collar, max.	1.5 mm ²
Wire cross-section, min. AWG	AWG 14	Wire cross-section, max. AWG	AWG 24
Stripping length	7.5 mm		

Classifications

ETIM 8.0	EC002780	ETIM 9.0	EC002780
ETIM 10.0	EC002780	ECLASS 14.0	27-14-11-52
ECLASS 15.0	27-14-11-52		

