

SAIH-CD-2X0.34/0.22-PVC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller offers a large and comprehensive range of sensor-actuator cables. We provide both, sensor cables as well as bus and valve cables of various sizes and lengths. If you cannot find a specific product or a product in the desired length, just contact us.

General ordering data

Version	Bus line, Number of poles: 4, 100 m, Shielded: Yes, Sheath material: PVC, Halogen: Yes
Order No.	1232650000
Type	SAIH-CD-2X0.34/0.22-PVC
GTIN (EAN)	4050118016383
Qty.	100 M

SAIH-CD-2X0.34/0.22-PVC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Net weight 52 g

Environmental Product Compliance

RoHS Compliance Status Compliant
 REACH SVHC No SVHC above 0.1 wt%

Technical specifications for cable

Cable length	100 m	Sheathing colour	violet
Resistance to oils	in accordance with IEC 60811-2-1	PE function	No
Suitable for cable carriers	No	Core cross-section	0.38 mm ²
Number of wires	4	Shielded	Yes
Halogen	Yes	Insulation	Polyolefin, PE
Acceleration	7 m/s ²	Bending radius, min., moving	10 x cable diameter
Bending radius, min., stationary	5 x cable diameter	Bending cycles	5 Mio
Wire cross section (Print/Online)	2 x 0.34 mm ² + 2 x 0.22 mm ²	Speed	180 m/min
Sheath material	PVC	Configurable cable length	No
Outer cladding in accordance with UL AWM style	2571 (80 °C)	Hybrid cable	Yes
Irradiation crosslinked	No	Welding spark resistance	No
Colour coding	white, blue, red, black	Temperature range, stationary	-40...80 °C
Resistant to welding beads	No	Temperature range, moving	-10...80 °C
Number of poles	4	Outside diameter	6.7 mm ± 0.3 mm

Cable specific standards

Impervious to smoke No

Standards

Impervious to smoke No

Cable structure

Sheathing colour	violet	Number of wires	4
Insulation cross-section	1.4 mm	Insulation	Polyolefin, PE
Material sheath	PVC	Wire pair shielding	Aluminium foil
Arrangement of wire cores	Twisted pair	Colour coding	white, blue, red, black
Complete shielding	Shielding braid made from copper wiring	Overlap of shielding braid	70 %
Wire material	tinned copper	Insulation diameter 2	2.05 mm

SAIH-CD-2X0.34/0.22-PVC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Electrical properties of cable

Insulation resistance	108 Ω	Category	Miscellaneous
Speed	180 m/min		

Mechanical and material properties of cable

Resistance to oils	in accordance with IEC 60811-2-1	UV-resistant	No
Halogen	Yes	Acceleration	7 m/s ²
Bending cycles	5 Mio	Speed	180 m/min
Impervious to smoke	No		

Classifications

ETIM 8.0	EC003249	ETIM 9.0	EC003249
ETIM 10.0	EC003249	ECLASS 14.0	27-06-18-01
ECLASS 15.0	27-06-18-01		


SAIH-CD-2X0.34/0.22-PVC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Detailed drawing



Pole scheme

