

IE-C5DB4WE0003MCSA70-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE lines, railway cable RW (reduced wire), cat. 5, PUR, black, RJ45 plug, no tools required, IP20 and M12 straight pin

General ordering data

| | |
|------------|---|
| Version | System cable, M12 D-code - IP 67 straight pin, RJ45 IP 20, Cat. 5e, Radox EM 104, 0.3 m |
| Order No. | 1220310003 |
| Type | IE-C5DB4WE0003MCSA70-E |
| GTIN (EAN) | 4050118350760 |
| Qty. | 1 items |

IE-C5DB4WE0003MCSA70-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Length | 0.3 m | Length (inches) | 11.811 inch |
| Net weight | 42.24 g | | |

Temperatures

| | | |
|--------------------------|-----------------------|----------------|
| Storage temperature | Operating temperature | -25 °C...70 °C |
| Installation temperature | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 67cf1078-beca-4687-860b-dc475a6ec24a |

Cable specific standards

| | | | |
|--|---|---|---|
| Fluorine content | According to EN 60684-2 Section 45.2 | Flames propagate vertically on bundled cables | in accordance with EN 50266, EN 50305, EN 60332-3-25, According to NF C32-070, 2.1, According to UL1685, 12 (FT4 exp.) |
| Multi-wire metallic data and control cable | According to EN50288-2-2 | Hydrogen halide content | According to EN-50267-2-1 |
| Corrosiveness of fumes | EN 50267-2-2 | Fire safety for railway vehicles | According to BS 6853, GM/RT 2130, Ia,Ib, II, According to EN 45545, HL1 - HL3, According to DIN 5510 1-4, According to NF F16-101, A1, A2, B, According to UNI CEI 11170, LR1-LR4, NFPA 130 |
| Impervious to smoke | According to BS 6853 Appendix D, According to IEC 61034-2, According to UL1685, 12 (FT4 exp.) | Poisonous gases | According to BS 6853 Appendix B |

General standards

| | |
|--------------------|-----------------|
| Connector standard | IEC 61076-2-101 |
|--------------------|-----------------|

Cable structure

| | | | |
|---|-----------------------------------|--------------------------|--------------|
| Wire connection cross section AWG, max. | AWG 22 | Sheathing colour | black |
| Cross-section | 4*AWG 22/7 - 0.32 mm ² | Shielding | SF/UTP |
| Number of wires | 4 | Insulation cross-section | 1.55 mm |
| Insulation | PE | Sheath diameter, max. | 7 mm |
| Sheath diameter, min. | 6.2 mm | Material sheath | Radox EM 104 |
| Colour coding | yellow, white, orange, blue | Wire material | Copper alloy |

IE-C5DB4WE0003MCSA70-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Electrical properties of cable

Category Cat. 5e

Mechanical and material properties of cable

| | | | |
|---------------------------------|---|--------------------------------|---------------------|
| Resistance to oils | in accordance with EN 50264-1 or EN 50306-1 | Halogen | No |
| Min. bending radius, repetitive | 6 *diameter | Min. bending radius, once only | 10 x cable diameter |
| Resistance to spread of flame | in accordance with IEC 60332-1-2, According to NF C32-070, 2.1, NFPA 130 | Corrosiveness of fumes | EN 50267-2-2 |
| Impervious to smoke | According to BS 6853 Appendix D, According to IEC 61034-2, According to UL1685, 12 (FT4 exp.) | | |

Plug, left

Plug left M12, D-coded, Number of poles: 4, IP67, male contact, straight, plug, Plastic, shielded

Plug, right

Plug right RJ45, IP20, male contact, straight, plug, Zinc diecast, shielded

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002599 | ETIM 9.0 | EC002599 |
| ETIM 10.0 | EC002599 | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 | | |

Drawings

Dimensioned drawing



Dimensional drawing



Wiring diagram

| RJ45 | | M12 | |
|------|--------|-----|--|
| 1 | yellow | 1 | |
| 3 | white | 2 | |
| 2 | orange | 3 | |
| 6 | blue | 4 | |

Detailed drawing



IE-C5DB4WE0003MCSA70-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Screwty® cable gland tool



The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

| | | | |
|------------|----------------------------|---------|---|
| Type | SCREWTY SET | Version | |
| Order No. | 1910000000 | | Cable gland tool for M8, M12 lines and connectors |
| GTIN (EAN) | 4032248436842 | | |
| Qty. | 1 ST | | |

Screwty® cable gland tool with torque function



The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

| | | | |
|------------|----------------------------|---------|---|
| Type | SCREWTY SET -DM | Version | |
| Order No. | 1920000000 | | Cable gland tool for M8, M12 lines and connectors |
| GTIN (EAN) | 4032248436859 | | |
| Qty. | 1 ST | | |

IE-C5DB4WE0003MCSA70-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Screwty® cable gland tool



The ideal tool for any application
 Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | SCREWTY- M12 | Version | |
| Order No. | 1900000000 | | Cable gland tool for moulded M12 lines |
| GTIN (EAN) | 4032248375868 | | |
| Qty. | 1 ST | | |

Screwty® cable gland tool with torque function



The ideal tool for any application
 Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | SCREWTY-M12-DM | Version | |
| Order No. | 1900001000 | | Cable gland tool for moulded M12 lines |
| GTIN (EAN) | 4032248436408 | | |
| Qty. | 1 ST | | |

IE-C5DB4WE0003MCSA70-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

TM HF 12 mm



The TM sleeves contain no halogens and virtually no pollutants. The sleeves are equipped with the TM-I 12 or TM-I 18 tags. They cover a wide range of applications for cables and lines. This system has particularly proved its worth in traffic engineering. The slim design guarantees firm seating on the conductor.

- Halogen-free
- The slim design guarantees firm seating on the conductor
- TMX 18 for mounting with cable-ties (width 3.6 mm)

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | TM 4/12 HF/HB | Version | |
| Order No. | 1719840000 | TM, Socket x 11.4 mm, Polyethylene LD, Colour: Transparent, | |
| GTIN (EAN) | 4008190353193 | Conductor O.D.: 6 - 10 mm | |
| Qty. | 500 ST | | |

TM HF 18 mm



The TM sleeves contain no halogens and virtually no pollutants. The sleeves are equipped with the TM-I 12 or TM-I 18 tags. They cover a wide range of applications for cables and lines. This system has particularly proved its worth in traffic engineering. The slim design guarantees firm seating on the conductor.

- Halogen-free
- The slim design guarantees firm seating on the conductor
- TMX 18 for mounting with cable-ties (width 3.6 mm)

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | TM 4/18 HF/HB | Version | |
| Order No. | 1719850000 | TM, Socket x 11.4 mm, Polyethylene LD, Colour: Transparent, | |
| GTIN (EAN) | 4008190353209 | Conductor O.D.: 6 - 10 mm | |
| Qty. | 500 ST | | |