

IE-C5DB4WE0065MCSA70-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Assembled IE lines, railway cable RW (reduced wire), cat. 5, PUR, black, RJ45 plug, no tools required, IP20 and M12 straight pin

General ordering data

Version	System cable, M12 D-code – IP 67 straight pin, RJ45 IP 20, Cat. 5e, Radox EM 104, 6.5 m
Order No.	1220310065
Type	IE-C5DB4WE0065MCSA70-E
GTIN (EAN)	4050118350869
Qty.	1 items

IE-C5DB4WE0065MCSA70-E

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	6.5 m	Length (inches)	255.9055 inch
Net weight	450 g		

Temperatures

Storage temperature		Operating temperature
Installation temperature	-50 °C...90 °C	

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Cable specific standards

Fluorine content	According to EN 60684-2 Section 45.2	Flames propagate vertically on bundled cables	in accordance with EN 50266, EN 50305, EN 60332-3-25, According to NF C32-070, 2.1, According to UL1685, 12 (FT4 exp.)
Multi-wire metallic data and control cable	According to EN50288-2-2	Hydrogen halide content	According to EN-50267-2-1
Corrosiveness of fumes	EN 50267-2-2	Fire safety for railway vehicles	According to BS 6853, GM/RT 2130, Ia,Ib, II, According to EN 45545, HL1 - HL3, According to DIN 5510 1-4, According to NF F16-101, A1, A2, B, According to UNI CEI 11170, LR1-LR4, NFPA 130
Impervious to smoke	According to BS 6853 Appendix D, According to IEC 61034-2, According to UL1685, 12 (FT4 exp.)	Poisonous gases	According to BS 6853 Appendix B

General standards

Connector standard	IEC 61076-2-101
--------------------	-----------------

Cable structure

Wire connection cross section AWG, max.	AWG 22	Sheathing colour	black
Cross-section	4*AWG 22/7 - 0.32 mm ²	Shielding	SF/UTP
Number of wires	4	Insulation cross-section	1.55 mm
Insulation	PE	Sheath diameter, max.	7 mm
Sheath diameter, min.	6.2 mm	Material sheath	Radox EM 104
Colour coding	yellow, white, orange, blue	Wire material	Copper alloy

IE-C5DB4WE0065MCSA70-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Electrical properties of cable

Category

Cat. 5e

Mechanical and material properties of cable

Resistance to oils

in accordance with EN 50264-1 or EN 50306-1

Halogen

No

Min. bending radius, repetitive

6 *diameter

Min. bending radius, once only

10 x cable diameter

Resistance to spread of flame

in accordance with IEC 60332-1-2, According to NF C32-070, 2.1, NFPA 130

Corrosiveness of fumes

EN 50267-2-2

Impervious to smoke

According to BS 6853 Appendix D, According to IEC 61034-2, According to UL1685, 12 (FT4 exp.)

Plug, left

Plug left

M12, D-coded, Number of poles: 4, IP67, male contact, straight, plug, Plastic, shielded

Plug, right

Plug right

RJ45, IP20, male contact, straight, plug, Zinc diecast, shielded

Classifications

ETIM 8.0

EC002599

ETIM 9.0

EC002599

ETIM 10.0

EC002599

ECLASS 14.0

27-06-03-08


ECLASS 15.0

27-06-03-08

Drawings

Dimensioned drawing

Dimensional drawing



Wiring diagram

Detailed drawing

RJ45		M12
1	yellow	1
3	white	2
2	orange	3
6	blue	4

