

THM PA 60/40 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

Version	THM, Device markers, 40 x 60 mm, white
Order No.	1244760000
Type	THM PA 60/40 WS
GTIN (EAN)	4050118032567
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2026-01-30T00:00:00+01:00

THM PA 60/40 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	40 mm	Height (inches)	1.5748 inch
Width	60 mm	Width (inches)	2.3622 inch
Net weight	773 g		

Temperatures

Operating temperature range -40...70 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Adhesive	Permanent acrylic copolymer		
Number per sheet	2000		
Printing method	Thermal transfer		
Version	Self-adhesive		
Width	60 mm		
UL 94 flammability rating	HB		
Operating temperature range, max.	70 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	No		
Basic material	Paper		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS		
Number of markers per combination	1 Label reel = Device markers		
Operating temperature range	-40...70 °C		
Number per roll	2000		

Device markers

Halogen No

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

