

IE-SW-BL05-4TX-1ST

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image



- Variations with 5 or 8 ports
- Variations for Gigabit Ethernet
- Sturdy metal housing
- Compact design
- Two redundant power inputs 12/24/48 V DC
- Variations with copper and fibre-optic interface (multi-mode and singlemode)
- Extensive approvals: CE, FCC, cULus, Class I Div. 2 / ATEX Zone 2, DNV-GL

General ordering data

Version	Network switch, unmanaged, Fast Ethernet, Number of ports: 4 x RJ45, 1 * ST Multi-mode, IP30, -10 °C...60 °C
Order No.	1240880000
Type	IE-SW-BL05-4TX-1ST
GTIN (EAN)	4050118028829
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Last order date	2027-01-30T00:00:00+01:00
Alternative product	IE-SW-BLB-05-4TX-1FESFP

IE-SW-BL05-4TX-1ST

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197
Certificate no. (cULusEX)	E223527

Dimensions and weights

Depth	70 mm	Depth (inches)	2.7559 inch
Height	115 mm	Height (inches)	4.5275 inch
Width	30 mm	Width (inches)	1.1811 inch
Net weight	175 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-10 °C...60 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	9229992a-00b9-4096-8962-200a7f33e289

EMC conformity and approvals

Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex ec IIC T4 Gc, EN IEC 60079-0, EN IEC 60079-7	Free fall	According to IEC 60068-2-32
EMC standards	EN 55032, EN 55035, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz - 6 GHz: 10 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 2 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8 PFMF: 100A/m	Vibration	according to IEC 60068-2-6
Shock	according to IEC 60068-2-27	Ship use	DNV
Safety standard	UL 61010-1, UL 61010-2-201, EN 62368-1		

IE-SW-BL05-4TX-1ST

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Environmental conditions

Operating temperature, max.	60 °C	Operating temperature, min.	-10 °C
Humidity	5 to 95 % (non-condensing)	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate	100 Mbps		
Transceiver type	Multimode		
Connector type	ST-Duplex		
Transmission distance, typ.	5 km		
Wavelength	typ.	1300 nm	
	Wavelength	TX	
	min.	1260 nm	
	max.	1360 nm	
	Wavelength	RX	
	min.	1100 nm	
Receive power	min.	-32 dBm	
	max.	-3 dBm	
Transmission power	min.	-20 dBm	
	max.	-10 dBm	
Link-budget	12 dB		

Guarantee

Time interval	5 years
---------------	---------

Interfaces

Fibre-optic ports	100BaseFX ports (ST connector), Multimode	RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port
Function DIP switch	1x for enabling/disabling the broadcast storm protection, QoS (on/off), MAC frame filtering (on/off)	Number of ports	4 x RJ45, 1 * ST Multimode
LED indicator	PWR1, PWR2, 10/100M (TP-Port), 100M (fibre-optic port).		

MTBF

MTBF	According to Standard	Telcordia (Bellcore), GB
	Operating time (hours), min.	3293423 h
	Ambient temperature	25 °C

Management features

Network traffic filter	Quality of Service (QoS)	Industrial protocol support	PROFINET device acc. to conformance class A
------------------------	--------------------------	-----------------------------	---

Power supply

Reverse polarity protection	Available
-----------------------------	-----------

IE-SW-BL05-4TX-1ST

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Supply voltage	12/24/48 V DC, 2 redundant inputs		
Current consumption	0.11 A at 24 V		
Overload current protection	1.1 A		
Connection type	1 removable 4-pin terminal block		
Voltage supply range	Voltage type	DC	
	Voltage, min.	9.6 V	
	Voltage, max.	60 V	

Switch characteristics

Priority queues	4	MAC table size	2 K
Packet buffer size	768 kBit	Bandwidth backplane	1 Gbit/s

Technical data

Housing main material	Aluminium	Type of mounting	DIN rail, Panel (with optional mounting kit)
Protection degree	IP30	Speed	Fast Ethernet
Switch	unmanaged		

Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) and 100BaseFX, IEEE 802.3x for flow control, IEEE 802.1p for Class of Service / Quality of Service (CoS/QoS)		

Classifications

ETIM 8.0	EC000734	ETIM 9.0	EC000734
ETIM 10.0	EC000734	ECLASS 14.0	19-17-04-02
ECLASS 15.0	19-17-04-02		

IE-SW-BL05-4TX-1ST

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

ST



Mounting rail outlet, ST junction design according to IEC 61754-2

General ordering data

Type	IE-XM-ST/ST	Version
Order No.	8808340000	Mounting rail outlet, fibre-optic, ST-ST coupler, IP20
GTIN (EAN)	4032248505920	
Qty.	1 ST	

Mounting kit for 19" rack assembly

- For assembling DIN rail-based devices on 19" racks



General ordering data

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 ST	

Mounting kit for wall mounting



Mounting kit for alternative wall-mounting of DIN rail-based (top-hat type) Industrial Ethernet components. IE-WALLMOUNT-KIT-30MM for use with:

- Industrial Ethernet Switches of the product range IE-SW-BL05

IE-WALLMOUNT-KIT-46MM for use with:

- Industrial Ethernet Switches of the product ranges IE-SW-BL06/BL08/VL05/VL08/VL09/VL16/PL06/PL08/PL09/PL10/PL16/PL18
- Industrial Ethernet media converters of the product range IE-MC-VL
- Industrial Ethernet switches of the product range IE-WL-AP

IE-SW-BL05-4TX-1ST

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

Type	IE-WALLMOUNT-KIT-30MM	Version	
Order No.	1504450000	Kit for wall mounting	
GTIN (EAN)	4050118312300		
Qty.	1 ST		

Ethernet



- Suitable for Cat. 5 (up to 100 MHz) and Cat. 6 (up to 250 MHz Class E)
- Suitable for PoE+ (according to IEEE 802.3at, IEEE 802.3bt Type 3 and 4)
- Protection of all wire pairs
- Connection via RJ45 sockets
- Metal housing

General ordering data

Type	VDATA CAT6	Version	
Order No.	1348590000	Terminal rail fixing, Surge protection, Cat.6, PoE, 802.3 bt at Type 1,	
GTIN (EAN)	4050118153002	802.3 bt at Type 2, 802.3 bt at Type 3, 802.3 bt at Type 4	
Qty.	1 ST		