

EBR-MODULE RS232

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Module for saving and loading a device configuration

- Reduced system downtime by simple reconfiguration if equipment is swapped over
- Automatic loading of the saved configuration possible after device restart
- Compact and robust design
- Useable with all Weidmüller managed switches and industrial WLAN devices

General ordering data

Version	Configuration module, IP40, 0 °C...60 °C
Order No.	1241430000
Type	EBR-MODULE RS232
GTIN (EAN)	4050118029086
Qty.	1 items

EBR-MODULE RS232

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Dimensions and weights

Depth	97 mm	Depth (inches)	3.8189 inch
Height	12 mm	Height (inches)	0.4724 inch
Width	32.5 mm	Width (inches)	1.2795 inch
Net weight	50 g		

Temperatures

Storage temperature	-20 °C...70 °C	Operating temperature	0 °C...60 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7cl
REACH SVHC	No SVHC above 0.1 wt%

EMC conformity and approvals

EMC standards	FCC Part 15, CISPR (EN55022) Class A, EN 61000-4-2 (ESD), Stage 2, EN 61000-4-3 (RS), Stage 3, EN 61000-4-4 (EFT), Stage 3, EN 61000-4-5 (surge voltage), Stage 3, EN 61000-4-6 (CS), Stage 3
---------------	---

Environmental conditions

Operating temperature, max.	60 °C	Operating temperature, min.	0 °C
Humidity	5 to 95 % (non-condensing)	Storage temperature, max.	70 °C
Storage temperature, min.	-20 °C		

Guarantee

Time interval	5 years
---------------	---------

Power supply

Connection type	RJ45-Port, RS232
-----------------	------------------

Technical data

Cable length	0.35 m	Type of fixing	M4 screw (< 4 mm)
Housing main material	PVC casting	Protection degree	IP40

EBR-MODULE RS232**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 8.0	EC001068	ETIM 9.0	EC001068
ETIM 10.0	EC001068	ECLASS 14.0	19-17-03-04
ECLASS 15.0	19-17-03-04		