

IE-SFP-1FEMLC-T

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image



- Supports DDM (Digital Diagnostic Monitoring)
- IEEE 802.3z compliant (Gigabit Ethernet SFPs)
- IEEE 802.3u compliant (Fast Ethernet SFPs)
- Symmetric LVPECL I/Os (Gigabit Ethernet SFPs)
- Symmetric PECL I/Os (Fast Ethernet SFPs)
- TTL signal detection indicator
- Pluggable in operation (hot pluggable)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Basic-, Value- and PremiumLine

General ordering data

Version	SFP Transceiver, 100 Mbps, Multimode, LC-Duplex, 4 km, -40 °C...85 °C
Order No.	1241450000
Type	IE-SFP-1FEMLC-T
GTIN (EAN)	4050118029192
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2027-01-30T00:00:00+01:00
Alternative product	IE-SFP-1FE-MM-2

IE-SFP-1FEMLC-T

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E230683

Dimensions and weights

Net weight	24 g
------------	------

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7cl
REACH SVHC	No SVHC above 0.1 wt%

EMC conformity and approvals

EMC standards	EN 55032, EN 55035	Ship use	DNV
Safety standard	UL 62368-1, EN 62368-1, EN 60825-1		

Environmental conditions

Operating temperature, max.	85 °C	Operating temperature, min.	-40 °C
Humidity	5 to 95 % (non-condensing)	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

Fibre optic transceiver characteristics

Transmission rate	100 Mbps	
Digital diagnostic monitor function (DDM)	Supported	
Transceiver type	Multimode	
Connector type	LC-Duplex	
Transmission distance, typ.	4 km	
Wavelength	typ.	1310 nm
	Wavelength	TX
	min.	1280 nm
	max.	1340 nm
	Wavelength	RX
	min.	1100 nm
Receive power	min.	-32 dBm
	max.	-3 dBm
Transmission power	min.	-18 dBm

IE-SFP-1FEMLC-T

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Link-budget	max. 14 dB	-8 dBm
-------------	------------	--------

Guarantee

Time interval	3 years
---------------	---------

Interfaces

Ethernet ports	1	Plug-in connector	Duplex-LC
Number of ports	Fast Ethernet, multi-mode, LC connector, 4 km		

Power supply

Supply voltage	3.3 V (via Ethernet switch)
----------------	-----------------------------

Technical data

Type of mounting	Insert in SFP slot
------------------	--------------------

Classifications

ETIM 8.0	EC003628	ETIM 9.0	EC003628
ETIM 10.0	EC003628	ECLASS 14.0	19-17-03-03
ECLASS 15.0	19-17-03-03		

IE-SFP-1FEMLC-T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

LC-Duplex



Mounting rail outlet, LC duplex junction design according to IEC 61754-20

General ordering data

Type	IE-TO-LCD-SM	Version	
Order No.	8947020000	Mounting rail outlet, fibre-optic, LC Duplex, Singlemode, IP20	
GTIN (EAN)	4032248735037		
Qty.	10 ST		