

CRIMPFIX L PZ3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- For automatic stripping and crimping
- Time-saving and efficient processing
- Easily adjustable to the respective cross-section range
- Stripping and crimping in one work step
- The processing of sleeves or contacts from other manufacturers can cause machine failures and defects!

General ordering data

| | |
|------------|--------------------------------|
| Version | Automatic stripper and crimper |
| Order No. | 1243790000 |
| Type | CRIMPFIX L PZ3 |
| GTIN (EAN) | 4050118031966 |
| Qty. | 1 items |

CRIMPFIX L PZ3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|--------------|
| Depth | 330 mm | Depth (inches) | 12.9921 inch |
| Height | 460 mm | Height (inches) | 18.1102 inch |
| Width | 390 mm | Width (inches) | 15.3543 inch |
| Net weight | 34000 g | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c, 7a, 7cl |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | d2df479e-2b79-4e98-adc7-b03577df98ae |

PW65 maintenance - automatic stripping/crimping

| | | | |
|---------------------------------------|--|---------------------------------------|-------------------------------|
| Stripping range | 0.5 - 2.5 mm ² (~AWG 20-14) | Drive | Electropneumatic |
| Pulse time | approx. 1 s | Wire end ferrules cross-section, max. | 2.5 mm ² |
| Wire end ferrules cross-section, min. | 0.5 mm ² | Crimping length | 8 mm |
| Consumables | loose cable lugs | Length of wire-end ferrule | 14 mm |
| Compressed-air connection | 5 - 5.5 bar | Electrical connection | 100-240 V / 50/60 Hz / 110 VA |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002778 | ETIM 9.0 | EC002778 |
| ETIM 10.0 | EC002778 | ECLASS 14.0 | 17-13-01-01 |
| ECLASS 15.0 | 17-13-01-01 | | |