


**SM 19/42 K MC NE GR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

For custom printing: Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

Version	SwitchMark, Device markers, 19 x 42 mm, grey
Order No.	<a href="#">1248640000</a>
Type	SM 19/42 K MC NE GR
GTIN (EAN)	4050118038972
Qty.	40 items

**SM 19/42 K MC NE GR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	1.2 mm	Depth (inches)	0.0472 inch
Height	19 mm	Height (inches)	0.748 inch
Width	42 mm	Width (inches)	1.6535 inch
Net weight	2.75 g		

**Temperatures**

Operating temperature range -40...60 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.020 kg CO2 eq.	

**General data**

Adhesive	Double-sided adhesive tape		
Material colour according to resistance code	8		
Version	Self-adhesive		
Width	42 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	60 °C		
Operating temperature range, min.	-40 °C		
Colour	grey		
Halogen	No		
Basic material	Polyamide 66		
Printed characters	without		
Number of markers per packaging unit	Form of supply	MultiCard	
compatible printer	<a href="#">PRINTJET CONNECT</a> , <a href="#">MCP BASIC 2</a> , <a href="#">MCP PLUS 2</a>		
Number of markers per combination	1 MultiCard = Device markers		
Operating temperature range	-40...60 °C		

**Device markers**

Halogen No

**Classifications**

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**Example of use**



Similar to illustration