

**KTB GP 22XX13V CD S4 6MM**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Similar to illustration**



Abbildung ähnlich

Integrate, expand and customise: The ideal expansion for every application

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

Flange plates

Flange plates in two thicknesses, for easy replacement of pre-assembl

**General ordering data**

|            |  |
|------------|--|
| Version    | Klippon TB (Terminal Box), flange plate, straight, Height: 177 mm, Width: 100 mm, Depth: 6 mm, Gland plates: left, right, Basic material: Stainless steel 1.4404, Stainless steel 1.4404 (316L), electropolished, silver |
| Order No.  | <a href="#">1256280000</a>   |
| Type       | KTB GP 22XX13V CD S4 6MM   |
| GTIN (EAN) | 4050118093704  |
| Qty.       | 1 items  |

**KTB GP 22XX13V CD S4 6MM**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**
**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 6 mm   | Depth (inches)  | 0.2362 inch |
| Height     | 177 mm | Height (inches) | 6.9685 inch |
| Width      | 100 mm | Width (inches)  | 3.937 inch  |
| Net weight | 865 g  |                 |             |

**Temperatures**

|                       |  |
|-----------------------|--|
| Operating temperature |  |
|-----------------------|--|

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**General information**

|                    |  |                       |   |
|--------------------|--|-----------------------|---|
| Material thickness | 6 mm                                     | Installation advice   | Screw mounting  |
| Surface finish     | electropolished                          | Basic material        | Stainless steel 1.4404,<br>Stainless steel 1.4404<br>(316L) |
| Integral fixing    | Screwed                                  | Protection class (UL) | Type 3, Type 4X, Type 12                                    |
| Gland plates       | left, right                              | Flange plate          | Yes   |
| Areas of use       | Explosive risk zone,<br>Process industry |                       |   |

**General information on accessories**

|                    |                 |                                 |   |
|--------------------|-----------------|---------------------------------|---|
| Material thickness | 6 mm            | Solder eyelet hole diameter (D) | 7 mm  |
| Surface finish     | electropolished | Basic material                  | Stainless steel 1.4404,<br>Stainless steel 1.4404<br>(316L) |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000211    | ETIM 9.0    | EC000211    |
| ETIM 10.0   | EC000211    | ECLASS 14.0 | 27-14-24-21 |
| ECLASS 15.0 | 27-14-24-21 |             |             |