

ADAPS M20-NPT1/2-W**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



ADAP series adaptors provide flexibility and versatility infilling unused entries in Ex equipment while maintaining Flameproof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

General ordering data

| | |
|------------|---------------------------------------------------------------------------------------|
| Version | ADAP (Klippon Ex adaptor), Adapter, straight, M 20 , 1/2" NPT, Stainless steel 1.4404 |
| Order No. | 1262040000 |
| Type | ADAPS M20-NPT1/2-W |
| GTIN (EAN) | 4050118093070 |
| Qty. | 16 items |

ADAPS M20-NPT1/2-W

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Width | 28.5 mm | Width (inches) | 1.122 inch |
| Length | 38 mm | Length (inches) | 1.4961 inch |
| Net weight | 56.65 g | | |

Temperatures

Operating temperature -50 °C...120 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Certificate numbers cable gland

| | | | |
|-------------------------------------|-----------------------------------------------------|------------------------------------|--------------------|
| Identification | II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da | Certificate no. cable gland (ATEX) | TÜV IT 16ATEX 059X |
| Certificate no. cable gland (IECEX) | IECEX TPS 16.0004X | Certificate no. cable gland (CCC) | 2020322313000069 |
| Certificate No. (IECEX) | IECEXTPS 16.0004X | | |

General information

| | | | |
|-----------------------------------|---------------------------|-----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Outer cable diameter, max. | 14 mm | Outer cable diameter, min. | 1 mm |
| O-Ring | Silicone | Tightening torque | 40 Nm |
| Silicone | Yes | Operating temperature range, max. | 120 °C |
| Operating temperature range, min. | -50 °C | Pitch of thread | 1.5 mm |
| Halogen | halogen-free | Standards | EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3 |
| AF size 1 | 26 mm | Protection degree | IP66 |
| Cable gland | M 20 | Basic material | Stainless steel 1.4404 |
| External thread | M 20 | Internal thread | 1/2" NPT |
| Length of thread | 16 mm | Explosion protection type | Ex d - flameproof, Ex e - increased safety |
| Installation guidelines | See assembly instructions | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000441 | ETIM 9.0 | EC000441 |
| ETIM 10.0 | EC000441 | ECLASS 14.0 | 27-14-08-06 |
| ECLASS 15.0 | 27-14-08-06 | | |