

**ADAP NPT1-1/2-M40-W****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



ADAP series adaptors provide flexibility and versatility infilling unused entries in Ex equipment while maintaining Flameproof Ex d and Increased Safety Ex e explosion protection and IP66/67/68 ingress rate.

**General ordering data**

|            |  |
|------------|--|
| Version    | ADAP (Klippon Ex adaptor), Adapter, straight, 1 1/2" NPT ,M 40, Brass, nickel-plated |
| Order No.  | <a href="#">1263240000</a>   |
| Type       | ADAP NPT1-1/2-M40-W  |
| GTIN (EAN) | 4050118092714  |
| Qty.       | 9 items  |

## ADAP NPT1-1/2-M40-W

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Width      | 55.5 mm  | Width (inches)  | 2.185 inch  |
| Length     | 22 mm    | Length (inches) | 0.8661 inch |
| Net weight | 119.09 g |                 |             |

## Temperatures

Operating temperature -50 °C...120 °C

## Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 69c399a3-d29f-4fa4-b22e-340c0db02257 |

## Certificate numbers cable gland

|                                     |   |                                    |                    |
|-------------------------------------|---|------------------------------------|--------------------|
| Identification                      | II 2G 1D, Ex db IIC Gb, Ex eb IIC Gb, Ex ta IIIC Da | Certificate no. cable gland (ATEX) | TÜV IT 16ATEX 059X |
| Certificate no. cable gland (IECEX) | IECEX TPS 16.0004X                                  | Certificate no. cable gland (CCC)  | 2020322313000069   |
| Certificate No. (IECEX)             | IECEXTPS16.0004X                                    |                                    |                    |

## General information

|                                   |                           |                                   |   |
|-----------------------------------|---------------------------|-----------------------------------|---|
| Tightening torque                 | 113 Nm                    | Operating temperature range, max. | 120 °C  |
| Operating temperature range, min. | -50 °C                    | Pitch of thread                   | 2.21 mm   |
| Halogen                           | halogen-free              | Standards                         | EN 60079-0, EN 60079-1, EN 60079-31, EN 60079-7, IEC 60079-0, IEC 60079-1, IEC 60079-31, IEC 60079-7, GB 12476.1, GB 12476.5, GB 3836.1, GB 3836.2, GB 3836.3 |
| AF size 1                         | 50 mm                     | Protection degree                 | IP66  |
| Cable gland                       | NPT 1-1/2"                | Basic material                    | Brass, nickel-plated  |
| External thread                   | 1 1/2" NPT                | Internal thread                   | M 40  |
| Length of thread                  | 16 mm                     | Explosion protection type         | Ex d - flameproof, Ex e - increased safety  |
| Installation guidelines           | See assembly instructions |                                   |   |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000441    | ETIM 9.0    | EC000441    |
| ETIM 10.0   | EC000441    | ECLASS 14.0 | 27-14-08-06 |
| ECLASS 15.0 | 27-14-08-06 |             |             |