

**KLBUE 15-32 CPF16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



With our wide range of KLBÜ shield connections, you can achieve flexible and self-adjusting shield contacting and ensure error-free plant operation.

**General ordering data**

Version	Clamping yoke, Clamping yoke for shield connection
Order No.	<a href="#">1252540000</a>
Type	KLBUE 15-32 CPF16
GTIN (EAN)	4050118104424
Qty.	10 items

## KLBUE 15-32 CPF16

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	64 mm	Depth (inches)	2.5197 inch
Height	32 mm	Height (inches)	1.2598 inch
Width	34.5 mm	Width (inches)	1.3583 inch
Mounting dimension - width	33.5 mm	Net weight	91.4 g

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.226 kg CO2 eq.	

### Material data

Colour	grey	UL 94 flammability rating	None
--------	------	---------------------------	------

### System specifications

End cover plate required	No	Mounting rail	TS 27
--------------------------	----	---------------	-------

### Additional technical data

Installation advice	C-rail with 16-mm opening	Explosion-tested version	No
Type of mounting	Screw		

### Conductors for clamping (rated connection)

Stripping length	32 mm	Type of connection	Spring connection
Number of connections	1	Cable diameter, max.	32 mm
Cable diameter, min.	15 mm	Connection cross-section, stranded, max.	32 mm <sup>2</sup>
Connection cross-section, stranded, min. 15 mm <sup>2</sup>			

### General

Installation advice	C-rail with 16-mm opening	Mounting rail	TS 27
---------------------	---------------------------	---------------	-------

### Rating data

Rated cross-section	32 mm <sup>2</sup>
---------------------	--------------------

### Classifications

ETIM 8.0	EC002020	ETIM 9.0	EC002020
ETIM 10.0	EC002020	ECLASS 14.0	27-25-01-20
ECLASS 15.0	27-25-01-20		